

## BC Pro 120V 1050VA 705W Standby UPS, Tower, USB port, 6 Outlets

MODEL NUMBER: BCPRO1050



### Highlights

- 1050VA / 1.05kVA tower 120V standby UPS
- Maintains AC output during power failures
- USB port, Front panel status LEDs, 97% efficient
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- BCPRO1050 UPS System
- USB cable
- Instruction manual

### Description

Tripp Lite's BCPRO1050 standby UPS offers AC surge suppression and long lasting battery support for desktop PCs, network workstations and a wide variety of consumer and professional electronics.

Uninterruptible Power Supply / UPS circuits switch to battery backup mode within milliseconds to keep connected equipment running without interruption or data loss during power failures, brownouts and overvoltages. AC surge suppression prevents connected equipment damage. USB communications port supports full featured monitoring and data-saving auto-shutdown options using Tripp Lite's free PowerAlert monitoring software.

### Features

- BCPRO1050 tower 120V standby UPS offers AC power protection from blackouts, brownouts, overvoltages and transient surges
- 1050VA / 705 watt UPS output capacity
- Uninterruptible Power Supply / UPS operation maintains battery-derived AC output during blackouts, brownouts and overvoltages to prevent data loss and system downtime for connected equipment
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [tripplite.eaton.com/products/power-alert](http://tripplite.eaton.com/products/power-alert)
- 7 minutes runtime at 100% load (705 watts), 23 minutes runtime at 50% load (355 watts)
- 107 minutes runtime for a desktop computer system consuming 80 watts continuous
- 6 built-in NEMA 5-15R UPS supported outlets
- NEMA 5-15P input connection with 6ft / 1.8m line cord
- Network grade AC surge protection is available from all outlets
- 97% line mode efficiency rating uses less energy and BTU emissions
- Front panel LEDs indicate line / battery mode, low battery, replace battery status; Audible alarm with alarm cancel / self-test button
- Hot swappable user battery replacement
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Tower housing supports desk or floor placement

## Specifications

OVERVIEW	
UPC Code	037332033376
UPS Type	Standby
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	6.4A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
OUTPUT	
Output Capacity (VA)	1050
Output Capacity (kVA)	1.05
Output Capacity (Watts)	705
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No
BATTERY	
Runtime Full Load (min.)	7 min. (705w)
Runtime Half Load (min.)	23 min. (355w)
Expandable Runtime	No
DC System Voltage (VDC)	18

Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-select-Tripp-Lite-Best-Liebert-Minuteman-other-UPS~RBC52">RBC52</a>&nbsp;  (quantity 3)
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, battery low/replace and overload status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	510
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	510
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems~UPSWM">UPSWM</a>&nbsp;  - tower mounting kit)
Primary UPS Depth (mm)	178
Primary UPS Height (mm)	286
Primary UPS Width (mm)	171
Shipping Dimensions (hwd / in.)	15.00 x 10.80 x 10.60
Shipping Dimensions (hwd / cm)	38.10 x 27.43 x 26.92
Shipping Weight (lbs.)	31.20
Shipping Weight (kg)	14.15
UPS Housing Material	Polycarbonate
UPS Power Module Dimensions (hwd, cm)	28.58 x 17.14 x 17.78
UPS Power Module Dimensions (hwd, in.)	11.25 x 6.75 x 7
UPS Power Module Weight (kg)	13.15



Powering Business Worldwide



UPS Power Module Weight (lbs.)	29
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	74
AC Mode Efficiency Rating (100% Load)	97%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	564
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	USB
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99
High Voltage Transfer to Battery Power (Setpoint)	143
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>APPLICATIONS</b>	
UPS Applications	Computer/Peripherals
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 &nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;&nbsp;



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.