

## HDBaseT Class B (HDBaseT-Lite) HDMI over Cat5e/6/6a Extender Kit, Power & IR Control, 4K x 2K 30 Hz UHD / 1080p 60 Hz, Up to 230 ft. (70 m), TAA

MODEL NUMBER: BHDBT-K-PI



Extends HDMI video/audio and IR control signals with Power over a single Cat5e/6/6a cable to a projector, monitor or television up to 230 ft. from the source.

### Description

The BHDBT-K-PI HDBaseT Class B (HDBaseT-Lite) HDMI over Cat5e/6/6a Extender Kit extends uncompressed HDMI audio and video and IR remote control signals up to 230-ft. (70.1 m) over a single Cat5e/6/6a cable, including video resolutions up to 1920 x 1080 (1080p). It also extends an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal up to 130-ft. (39.62 m). In addition to HDMI and IR signals, this extender kit features built-in PoE technology, which powers the receiver over Cat5e/6/6a cable, eliminating the need for an external power source.

The two-way IR remote control feature (@ 39 KHz) lets you control your Blu-ray player or other HDMI source using its remote when at the remote monitor or control your remote monitor using its remote when at the Blu-ray player. Locking HDMI ports (ideal for use with Tripp Lite's P569-006-LOCK high-speed HDMI cables with locking connectors) on both the transmitter and receiver prevent cables from coming loose or undone, ensuring an intact signal.

The plug-and-play BHDBT-K-PI supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio, as well as 3D video, EDID and HDCP. Attach the transmitter and receiver units to a wall, rack or pole with the included mounting hardware.

### Features

#### Extends HDMI Video/Audio and IR Control Signals with Power Over a Single Cat5e/6/6a Cable

- Ideal for digital signage, classrooms, retail locations, conference rooms and trade show booths
- Extends an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal up to 130-ft. (39.62 m)
- Extends a high-definition 1920 x 1080 (1080p) signal up to 230-ft. (70.1 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio
- Supports 3D video, EDID and HDCP
- Reduces cable clutter and installation costs
- Built-in PoE technology powers receiver over Cat5e/6/6a cable, eliminating need for external power source

### Highlights

- Ideal for digital signs, classrooms and trade show booths
- Extends both a 4096 x 2160 and 3840 x 2160 (4K x 2K) @ 30Hz signal up to 130-ft. (39.62 m)
- Extends a 1920 x 1080 (1080p) signal up to 230-ft. (70.1 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Built-in PoE technology powers receiver over Cat5e/6/6a cable

### Package Includes

- Transmitter unit
- Receiver unit
- IR-IN cable, 5-ft. (1.52 m)
- IR-OUT cable, 6-ft. (1.83 m)
- External Power Supply with C14 inlet (Input: 100-240V, 50/60 Hz, 1.5A; Output: 48V, 1A), 4.5-ft. (1.37 m)
- C13 to NEMA 5-15P power cord, 6-ft. (1.83 m)
- Mounting hardware
- Owner's manual

#### Controls IR Devices

- 2-way 39 KHz IR remote control functionality lets you control your Blu-ray player with its remote while standing at the remote monitor (and vice versa)

#### Locking HDMI Ports on Transmitter and Receiver

- Prevent cables from coming loose or disconnected, ensuring an intact signal
- Ideal for use with Tripp Lite's P569-006-LOCK high-speed HDMI cables with locking connectors

#### Easy to Set Up and Use

- Plug and play with no software or drivers to download and install
- Includes mounting hardware for attaching each unit to a wall, rack or pole

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332186935
Product Type	Extender Kit
Accessory Type	Extender Kit
Technology	HDBaseT; HDMI; IR; Cat5/5e; Cat6; POC
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K @ 30Hz)
Max 720P Range (ft)	230
Max 1080P Range (ft)	230
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	130
Max 3840 x 2160 (4K@30Hz) Range (ft)	130
Transmitter Video Input	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Recommended Cabling	HDMI
Max Supported Color Depth	36-bit Deep Color

HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
<b>AUDIO</b>	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	7.1 Channel Surround Sound, DTS-HD and Dolby TrueHD
<b>INPUT</b>	
Bus Powered	No
<b>POWER</b>	
Power Source Type	AC Adapter with detachable power cord
External Power Supply Plug(s)	IEC-320-C14
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 2A
External Power Supply Output Specs (V / A)	48V / 1.04A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
AC Plug Type	NEMA 5-15P
Power Source	Transmitter end only (Included)
Power Over Cable (PoC) Support	Yes
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 48V, 1A, 4.5ft.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	RJ45 INPUT/OUTPUT (GREEN / POWER, ORANGE / LINK) ACTIVITY (FLASHING ORANGE WHEN TX/RX POWERED AND CONNECTED) HDMI LINK (GREEN WHEN SIGNAL IS BEING SENT FROM SOURCE TO DISPLAY) POWER (GREEN)
<b>PHYSICAL</b>	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket <a href="http://www.tripplite.com/din-rail-mounting-bracket-for-digital-signage-version-2-B110-DIN-02">B110-DIN-02</a>
Form Factor/Mounting Options	Box; Wall-mount

Receiver Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Receiver Unit Weight (lbs.)	1.7
Shipping Dimensions (hwd / in.)	8.43 x 5.91 x 3.19
Shipping Dimensions (hwd / cm)	21.41 x 15.01 x 8.10
Shipping Weight (lbs.)	2.95
Shipping Weight (kg)	1.34
Transmitter Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Transmitter Unit Weight (lbs.)	1.7
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	1.7
Unit Weight (kg)	0.77
Housing	Metal
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	0% TO 85% RH, Non-Condensing
Operating Humidity Range	0% TO 85% RH, Non-Condensing
Storage Humidity Range	0% TO 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	230
Max 480P Range (ft)	230
Max 1440 x 900 Range (ft)	230
Max 1080i Range (ft)	230
Max 1920 x 1440 Range (ft)	130
Max 4K UHD Range (ft)	130
Max 480i Range (ft)	230
Max 640 x 480 Range (ft)	230
Max 800 x 600 Range (ft)	230
Max 1600 x 1200 Range (ft)	230
Max 2048 x 1536 Range (ft)	130
EDID Compatible	Yes
IR Remote Extension Support	Yes

RS-232 Serial Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
HDCP Specification	1.4
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
External Power Supply Certifications	UL; cUL; PSE; FCC; CE; TUV; LPS; RoHS; WEEE
Product Compliance	RoHS; REACH; FCC (USA); Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty