

180V Extended Battery Module (EBM) for SmartOnline UPS Systems, 3U Rack/Tower, TAA

MODEL NUMBER: BP180RT3UTAA



Provides extended runtime for compatible UPS systems in education, healthcare, military, government and other network applications requiring TAA compliance.

Features

Backup Battery Module Gives Your Compatible UPS System Extended Runtime

The valve-regulated lead-acid (VRLA) BP180RT3UTAA offers extended battery runtime when used in conjunction with the SU6000RT3UTAA SmartOnline UPS system. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Versatile Installation Options

You can mount the hot-swappable BP180RT3UTAA in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included support stands.

TAA-Compliant for GSA Schedule Purchases

The BP180RT3UTAA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	786689875756
INPUT	
Input Phase	Single-Phase
UPS Input Cord Length (ft.)	1
UPS Input Cord Length (m)	0.3
Input Cord Details	15.7 in. connector cord

Highlights

- Connects to SU6000RT3UTAA SmartOnline® UPS system to add critical runtime
- Includes heavy-gauge battery cabling with high-current 180V DC connectors
- Daisy-chain connector supports additional battery packs for even longer runtime
- Supports 3U rack mounting or upright tower installation with included support stands
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Compatible only with SU6000RT3UTAA SmartOnline UPS system

Package Includes

- 180V Extended Battery Module
- External battery cable
- Rack-mounting hardware
- Tower support stands
- Quick start guide



Powering Business Worldwide

TRIPP LITE
SERIES

OUTPUT	
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Expandable Runtime	Yes
DC System Voltage (VDC)	180
Replacement Battery Cartridge	744-A1974
Battery Replacement Description	Hot-swappable, user replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
UPS Connection	UPS specific DC connector
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (RK2PC)
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.400
Unit Weight (lbs.)	150.000
Unit Weight (kg)	68.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	UL 1778; cTUVus
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

Extended Service Plans	<p>5-year EBM depot exchange plan: TL9SW5Y-18000BCExpedited parts coverage for 5 yearsParts, electronics, and EBM battery coverageNext business day shippingTechnical supportPurchase of matching service plan for connected UPS required</p> <p>5-year EBM onsite plan: TLWEBN75XX-7000BCOnsite parts and labor coverage for 5 yearsParts, electronics, and EBM battery coverage24x7 onsite labor coverage, next-day responseNext-day shippingTechnical supportPurchase of matching service plan for connected UPS required</p> <p>3-year depot exchange and onsite plans also available</p>
------------------------	--

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.