

## External 240V 3U Rack/Tower Battery Pack Enclosure + DC Cabling for select UPS Systems (BP240V10RT3U)

MODEL NUMBER: BP240V10RT3U



Need more runtime? The BP240V10RT3U external battery pack extends the runtime of compatible Tripp Lite UPS Systems and has a rear connector for daisy-chaining multiple battery packs together to achieve an even longer runtime. Installation is quick, simple and versatile—the battery pack can be adapted to rackmount (3U), tower or stack form factors.

### Description

BP240V10RT3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 240V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 240V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - SU6000RT3U, SU6000RT3UHV, SU8000RT3U, SU8000RT3U1TF, SU8000RT3UG, SU8000RT3UHW, SU8000RT3UN50, SU8000RT3UN50TF, SU10000RT3U, SU10000RT3U2TF, SU10000RT3UG, SU10KRT3U, SU10KRT3UHV, SU10K3/1INTPM, SU16KRT, SU16KRT-1TF, SU16KRT8, SU16KRTG, SU16KRTHW, SU20KRT, SU20KRT-1TF, SU20KRT8, SU20KRTG, SU20KRTHW and other Tripp Lite UPS systems that specify the use of this battery pack.

### Features

- Offers extended-run UPS operation when used in conjunction with compatible 240V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 240V external battery packs to the host UPS
- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced 2 point center-mounting in 2 post equipment racks
- 2-9USTAND option enables upright tower placement

## Specifications

### Highlights

- Extends the runtime of expandable 240V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

### Package Includes

- BP240V10RT3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

<b>OVERVIEW</b>	
UPC Code	037332115843
<b>INPUT</b>	
Input Phase	Single-Phase
<b>BATTERY</b>	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple battery packs
Expandable Runtime	Yes
DC System Voltage (VDC)	240
UPS Connection	Detachable cable with UPS specific DC connector (91.4 cm length, 6 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
<b>PHYSICAL</b>	
Material of Construction	Steel
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="//www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2POSTRMKITHD</a> ); Tower ( <a href="//www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> )
Minimum Required Rack Depth (cm)	83.82
Minimum Required Rack Depth (inches)	33
Shipping Dimensions (hwd / in.)	11.50 x 23.00 x 33.00
Shipping Dimensions (hwd / cm)	29.21 x 58.42 x 83.82
Shipping Weight (lbs.)	184.00
Shipping Weight (kg)	83.46
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 25.000
Unit Dimensions (hwd / cm)	13.34 x 44.45 x 63.5
Unit Weight (lbs.)	158.70
Unit Weight (kg)	71.99
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe)
<b>WARRANTY &amp; SUPPORT</b>	

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.