

Multi-Device UV Charging Station, Hospital-Grade, 16 USB Ports, iPad and Android Tablets, Antimicrobial, White

MODEL NUMBER: CS16USBWHG



Charges, syncs, secures, organizes and sanitizes up to 16 USB devices in healthcare, education, retail, warehouse and office settings.

Features

Wall-Mount Charging Cabinet Accommodates up to 16 USB Mobile Devices This 120V charging station provides USB charging, secure storage, cord management and surface sanitization for as many as 16 iPad, iPod, iPhone, Android, Surface, Kindle and other USB tablets and smartphones. The USB ports deliver the fastest charging supported by each connected device, up to 2.4A per port. A USB uplink port connects to a host computer for wired syncing. The tablet charging station is recommended for healthcare facilities, classrooms, businesses, government agencies, restaurants, hotels and anywhere else that uses mobile devices on a daily basis.

UV Light Helps Sanitize Devices without Potentially Dangerous Heat, Liquids or Chemicals The CS16USBWHG helps reduce the presence of germs on Chromebooks, laptops and tablets. Built-in ultraviolet lights help disinfect electronic devices at the touch of a button by destroying most microbes without the use of damaging heat, liquids or chemicals. The germicidal UVC bulbs are on a timer to control the amount of UV exposure the devices receive. An LED on the exterior of the cabinet indicates when the doors are closed and the start button can be pressed to activate the 10-minute timer. A second LED indicates when the UVC lights are on. If a door is opened during sanitization, the lights automatically shut off for safety.

Exclusive, Patented Antimicrobial Protection Fights Surface Bacteria The charging cabinet's interior and exterior surfaces are protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and viruses, such as C. diff and MRSA. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure Constructed from heavy-duty steel, this charging cabinet provides safe, secure storage. The split front doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Mounts Easily to the Wall of a Nurse's Station, Classroom or Back Office Four rear keyhole cutouts allow efficient wall mounting. Cutouts accommodate M5 or 3/16-inch bolts (not included) and are spaced 16 inches apart horizontally and 12 inches vertically to match standard wall studs. The CS16USBWHG also supports stationary desktop or floor placement installations. You can also convert it to a mobile cart with Tripp Lite's optional non-antimicrobial CSHANDLEKIT2 (sold separately), and roll it where needed.

Well-Organized to Avoid Confusing Cable Clutter Cables and connectors run through strain relief bushings, keeping them organized and out of the way, and are protected by blanking panels. Adjustable

Highlights

- 16 internal USB-A ports charge mobile devices with optimum charge level up to 2.4A
- Ultraviolet (UVC) lights help disinfect devices without use of damaging heat or chemicals
- Patented antimicrobial coating is 99.9% effective in inhibiting bacteria and viruses
- Steel enclosure locks with included keys to discourage theft, damage and tampering
- 10-ft. (3.05 m) cord with NEMA 5-15P HG plug allows great flexibility in reaching AC outlets

Applications

- Charge up to 16 Apple, Android, Microsoft, Amazon and other USB tablets and smartphones in medical facilities, schools, businesses and government organizations that rely on the daily use of mobile devices
- Sanitize your devices with ultraviolet light to reduce the presence of germs

Package Includes

- CS16USBWHG Hospital-Grade 16-Device UV Charging Cabinet, White
- (2) Keys
- Owner's manual



dividers accommodate up to 16 devices. Front doors open at least 180 degrees to allow maximum access to the interior. Access grommets allow the 10-ft. (3.05 m) cord with hospital-grade NEMA 5-15P plug to extend through either side of the cart, allowing great flexibility in reaching AC outlets.

Specifications

OVERVIEW	
UPC Code	037332240132
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure; Sync; Sanitize
Device Compatibility	Tablet; Phone
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Input Connection Type	C14 inlet with 110-240V AC compatibility. Also accepts user-supplied country-specific AC cordsets
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	16
Overcharge Protection	Yes
Total Charging Amps	40A
Charging Method	USB
Charging Ports Detail	Pass through
Charging Port Type	USB A (FEMALE)
Charging Amps per Port	2.4A
PHYSICAL	
Antimicrobial Coating	Yes
Color	White
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	24.53 x 33.66 x 23.62
Shipping Weight (kg)	50.50



Slot Dimensions (hwd / in.)	10.6 x 1.5 x 15.4
Slot Dimensions (hwd / mm)	268.1 x 38.2 x 390.5
Unit Dimensions (hwd / cm)	47.75 x 77.04 x 54.86
Unit Dimensions (hwd / in.)	18.8 x 30.33 x 21.6
Unit Weight (kg)	38.40
Unit Weight (lbs.)	84.66
Number of Shelves	1
ENVIRONMENTAL	
Power Consumption (Watts)	56W
SPECIAL FEATURES	
Cord Management	No
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key; Padlock (User Supplied)
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>