

## Multi-Device Charging Station, 32 AC Outlets, Chromebooks and Laptops, Wall-Mount Option, Black

MODEL NUMBER: **CS32ACMX**



Locking steel charging station for AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. Recommended for education, office, commercial, retail, industrial and healthcare environments.

### Description

The CS32ACMX 32-Device AC Charging Station provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

32 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. Their AC adapters plug into the cart's 32 NEMA 5-15R outlets as needed. The integrated charging timer allows for rotational charging between the two zones of equipment. The CS32ACMX also charges tablets and other USB devices through their power adapters. A built-in circuit breaker protects against overloads. A built-in RJ45 connector allows for the hookup of network equipment. The 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets to help you place the cabinet in a convenient location.

The charging station promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering, and flow-through ventilation helps prevent overheating.

The charging station also encourages clutter-reducing organization of devices and cabling. AC outlets, power adapters and cords store out of sight.

The charging station is easy to configure and ships ready for quick and easy installation. The split front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable shelf dividers accommodate thicker devices.

### Features

#### Convenient Charging

- Charges 32 Chromebooks and laptops up to 15 in. screen size
- Device power adapters plug into NEMA 5-15R outlets
- Included charging timer rotates charging between device shelves
- Built-in RJ45 connector to allow for network equipment hookup
- Also charges tablets and other USB devices through their power adapters
- Built-in circuit breaker protects against overloads
- 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

### Highlights

- Charges 32 Chromebooks and laptops up to 15 in. screen size
- Charging timer facilitates rotational charging between shelves
- Two external outlets that can be switched off internally
- Built-in RJ45 connector to allow for network equipment hookup
- Secures devices in locking, vented, all-mountable steel cabinet
- Protective shelves with removable dividers and cord management
- Ships ready for quick, easy installation

### Package Includes

- CS32ACMX 32-Device AC Charging Station Cart, Black
- Input cord wrap
- (2) Keys
- Owner's manual

**Comprehensive Protection**

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- 2-point locking mechanism latches doors at top and bottom
- Built-in hasp and user-supplied padlock can replace or supplement built-in lock
- Rear ports accommodate user-supplied bicycle cable or chain lock
- Flow-through ventilation helps prevent devices from overheating
- Protective shelves specially coated to avoid device scratches and scuffs
- Cord access ports with rubber grommets protect against abrasions
- Solid top work surface helps avoid accidental drips and spills that could damage devices

**Clutter-Reducing Organization**

- AC outlets, power adapters and cords store out of sight
- Lockable trim panels provide theft deterrent plus quick access to AC adapters and cords
- Shelves include charging cord access ports for each device
- Staggered outlets fit power adapters without blocking adjacent outlets

**Flexible Configuration**

- Ships ready for quick, easy installation
- Split front doors open 180 degrees for improved device and service access
- Rear-panel mounting slots support optional wall-mount installation
- Removable dividers accommodate thicker devices like battery chargers

## Specifications

OVERVIEW	
UPC Code	037332224316
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Charger Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Connection Type	5-15P con cable de alimentación de 2m
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05

<b>OUTPUT</b>	
Output Receptacles	(5) 5-15R
Overload Protection	Breaker de 15A
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Disyuntor de combinación de CA e interruptor general de encendido y apagado de dos posiciones con iluminación roja; disyuntor individual de grupo de carga
LED Indicators	Temporizador de carga con 4 indicadores independientes: encendido/apagado general, grupo de carga 1 en operación, grupo de carga 2 en operación, encendido/apagado de tomacorrientes externos.
<b>CHARGING</b>	
Number of Charging Ports	32
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 12A
Overcharge Protection	No
Charging Amps per Port	12A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	45.08 x 22.83 x 33.66
Shipping Dimensions (hwd / cm)	114.50 x 57.99 x 85.50
Shipping Weight (lbs.)	157.04
Shipping Weight (kg)	71.23
Slot Dimensions - Bottom (hwd / mm)	266.7 x 38.2 x 390.5
Slot Dimensions - Top (hwd / mm)	266.7 x 38.2 x 390.5
Unit Dimensions (hwd / cm)	89.15 x 95.33 x 51.05
Unit Weight (kg)	52.16
Number of Shelves	2
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No



Powering Business Worldwide



Flow-Through Ventilation	Yes
Over Current Protection	420 Joules
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); UL 1363
Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.