

Safe-IT 36-Device UV Mobile Charging Cart for Laptops and Chromebooks - 120V, NEMA 5-15P, 10 ft. (3.1 m) Cord, Antimicrobial, Wood-Grain Top, White

MODEL NUMBER: CSC36VACUVC



Charges, secures, organizes and UV-sanitizes up to 36 Chromebooks, tablets and laptops in education, healthcare, retail and office environments.

Features

Mobile Charging Cart Accommodates up to 36 Chromebooks, Tablets and Laptops

The CSC36VACUVC charging cart provides timed AC charging, secure storage, UVC sanitization and cord management for as many as 36 Chromebooks, tablets and laptops. The connected devices' AC adapters plug into 36 NEMA 5-15R outlets. Built-in circuit breakers protect the devices against overloads.

High-Speed Zone Charging Conserves Energy and Helps Avoid Potential Overloads

The 36 NEMA 5-15R outlets are split evenly into two color-coded charging zones to support more devices and higher wattages without overloads. A built-in timer alternates charging zones every hour. LEDs indicate which zone is being charged at any given time.

UVC Light Helps Sanitize Devices without Potentially Dangerous Heat, Liquids or Chemicals

The CSC36VACUVC helps reduce the presence of germs on your laptops, Chromebooks, tablets and AV equipment. Built-in ultraviolet lights help disinfect devices at the touch of a button by destroying most microbes without the use of damaging heat, liquids or chemicals. The germicidal UVC bulbs are on a timer to control the amount of UVC exposure the devices receive. An LED on the exterior of the cabinet indicates when the doors are closed and the start button can be pressed to activate the 10-minute timer. A second LED indicates when the UVC lights are on. If a door is opened during sanitization, the lights automatically shut off for safety.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ charging cart features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Moving Your Devices from Room to Room Is Easy

Large swivel casters with non-marking wheels improve the ride over uneven surfaces, including carpeting and thresholds, and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control. Corner safety bumpers protect walls and doorways from scratches. The compact cart takes up about the same amount of physical space, or even less, as a typical A/V cart.

Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure

Highlights

- Internal NEMA 5-15R outlets provide safe charging for up to 36 laptops and tablets
- Hourly timer alternates charging zones to help prevent overloads
- Ultraviolet (UVC) lights help disinfect devices without use of damaging heat or chemicals
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew
- Steel enclosure locks with included keys to discourage theft, damage and tampering

Package Includes

- CSC36VACUVC 36-Device UV Mobile Charging Cart
- Reversible handle
- (4) Metal casters
- (2) Safety corner bumpers
- (2) Power cord manager wire forms
- (12) M6 x 12 mm hex screws
- (4) M6 x 20 mm hex screws
- (16) M8 x 20 mm hex screws
- (4) Flat washers
- Hex key
- (4) Sleeve spacers
- (4) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Constructed from heavy-duty steel covered with a white powder-coated finish, this charging cart provides safe, secure storage. Devices and their power adapters are stored in separate compartments. The front and back doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Well-Organized to Avoid Confusing Cable Clutter

Heavy power adapters store out of the way in removable baskets. Cables and connectors run through zoned slots and an overhead cable manager, keeping them organized and out of the way. Adjustable dividers accommodate up to 18 devices per shelf. A power cord wrap keeps the input cord out of the way when moving the charging station. The 10-foot cord with space-saving right-angle NEMA 5-15P plug allows great flexibility in reaching AC outlets.

Laminated Wood-Grain Top Doubles as a Convenient Workstation

The laminated top acts as a smooth writing surface and holds a projector, monitor or other peripherals that plug into two external NEMA 5-15R outlets controlled by an inside on/off switch.

Specifications

OVERVIEW	
UPC Code	037332274229
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Charger Functions	Charge; Sanitize; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	36
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
POWER	
Power Consumption (Watts)	38.00
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	DOOR CLOSED / "READY" LED: GREEN UV LIGHT "ON" LED: RED POWER - GREEN
CHARGING	



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Charging Ports	36
Charging Method	AC
Charging Port Type	(36) NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(36) 12A
Charging Amps per Port	12A
PHYSICAL	
Color	White
Material of Construction	Steel
Charging Station Form Factor	Mobile Cart
Slot Dimensions (hwd / in.)	13.04 x 1.08 x 19.25
Unit Dimensions (hwd / in.)	46.420 x 30.550 x 37.860
Unit Weight (lbs.)	288.81
Unit Weight (kg)	131.00
Number of Shelves	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	Yes
Locking	Yes
Lock Type	Key; Padlock (User Supplied)
LED Lights	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); UL 62368-1
Product Compliance	RoHS
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (U.S. & Canada)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	Yes

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.