

10-Device Desktop AC Charging Station with Surge Protector for Tablets, Laptops and E-Readers

MODEL NUMBER: **CSD1006AC**



Locking enclosure provides AC charging, secure storage and cord management for up to 10 tablets, laptops and e-readers. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSD1006AC 10-Device Desktop AC Charging Station provides AC charging, secure storage and cord management for up to 10 tablets, laptops and e-readers up to 10.5 inches. Each slot is 1 1/4" wide. It's recommended for schools, offices, warehouses, retail outlets, worksites, healthcare facilities and anywhere else multiple mobile devices are used.

Devices fit into slots 1.25 inches wide. Their AC adapters plug into the 10 widely spaced NEMA 5-15R outlets as needed for proficient charging. The devices are protected by 2,880 joules of surge suppression and EMI/RFI noise filtering that protect against potentially harmful bursts in voltage. Diagnostic LEDs let you know that the charging station is grounded and the connected devices protected. An auto-shutoff feature cuts off power to the outlets in case of a power spike.

The CSD1006AC locks with the included keys to help prevent theft, damage or tampering. A cable with combination lock is also included to secure the charging station to a desk, table, cart or other flat surface. The 6-ft. (1.83 m) AC input cord with NEMA 5-15P plug helps you place the charging station in a convenient location. Storage shelf dividers are easily removed to accommodate thicker devices. Cabling is secured beneath the shelf tray to alleviate clutter.

The CSD1006AC comes with a 1-year lifetime warranty. The included Surge Suppressor comes with a lifetime limited warranty and \$100,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only).

Features

Convenient AC Charging

- 10 NEMA 5-15R outlets for charging tablets, laptops and e-readers up to 10.5 in.
- Devices fit into slots 1.25 in. wide
- 6-ft. (1.83 m) AC input cord with right-angle NEMA 5-15P plug reaches convenient outlets
- Recommended wherever multiple mobile devices are used—schools, offices, warehouses, etc.

Comprehensive Protection

- 2,880 joules of surge suppression
- EMI/RFI noise filtering

Highlights

- 1.25 in. wide slots hold devices up to 10.5 in.
- 6-ft. (1.83 m) AC input cord with right-angle NEMA 5-15P plug
- 2,880 joules of surge suppression
- Locking lid helps prevent device theft, damage or tampering
- Separate cable with combination lock for added security

Package Includes

- CSD1006AC 10-Device Desktop AC Charging Station
- Enclosure unit with locking lid
- Combination cable lock
- (2) Keys
- Owner's manual



Powering Business Worldwide



- Diagnostic LEDs indicate grounded connection and protected outlets
- Automatically shuts down outlets in case of power surge

Complete Security

- Locks with included keys to help prevent device theft, damage or tampering
- Included combination cable lock secures the unit to a desk or cart

Clutter-Reducing Organization

- AC outlets, power adapters and cords store out of sight
- Staggered outlets fit power adapters without blocking adjacent outlets
- Storage shelf dividers can be removed to accommodate thicker devices

Included Surge Suppressor Protected by Lifetime Limited Warranty and Insurance

- \$100,000 of Ultimate Lifetime Insurance for any connected equipment damaged by a power surge (U.S., Canada and Puerto Rico only)

Specifications

| OVERVIEW | |
|------------------------------------|----------------------|
| UPC Code | 037332193469 |
| Product Type | Multi-Device Charger |
| Charging Form Factor | Desktop Cabinet |
| Charger Functions | Charge; Secure |
| Device Compatibility | Laptop; Tablet |
| Device Slots | 10 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V |
| Input Plug Features | 120V/15A |
| Voltage Compatibility (VAC) | 120 |
| Input Frequency | 60 Hz |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.83 |
| OUTPUT | |
| Frequency Compatibility | 60 Hz |
| Circuit Breaker (amps) | 15 |



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| CHARGING | |
|---------------------------------|-------------------------|
| Number of Charging Ports | 10 |
| Charging Method | AC |
| Charging Port Type | NEMA 5-15R |
| Charging Ports Details | Pass through |
| Charging Ports / Amps | (10) 15A |
| Overcharge Protection | Yes |
| Charging Amps per Port | 15A |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 2880 |
| AC Suppression Response Time | <1ns |
| Automatic Shut-Off | Yes |
| PHYSICAL | |
| Color | Black; Gray |
| Material of Construction | Plastic |
| Charging Station Form Factor | Desktop Cabinet |
| Shipping Dimensions (hwd / in.) | 10.50 x 16.40 x 17.70 |
| Shipping Dimensions (hwd / cm) | 26.67 x 41.66 x 44.96 |
| Shipping Weight (lbs.) | 13.65 |
| Shipping Weight (kg) | 6.19 |
| Unit Dimensions (hwd / in.) | 8.940 x 16.540 x 13.540 |
| Unit Dimensions (hwd / cm) | 42.01 x 34.39 x 22.71 |
| Number of Shelves | 1 |
| FEATURES & SPECIFICATIONS | |
| Antimicrobial | No |
| Built-In Circuit Breaker | Yes |
| Cord Management | No |
| Overcurrent Protection | Yes |
| EMI/RFI Line Noise Protection | Yes |
| Flow-Through Ventilation | Yes |
| IP68 Rated | No |
| IP20 Rated | No |
| UV Sterilization | No |

| | |
|---|--|
| Locking | Yes |
| Lock Type | Key; Combination Cable Lock |
| STANDARDS & COMPLIANCE | |
| Product Certifications | UL 1449 |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |
| Product Warranty Period (U.S. & Canada) | 1-year limited warranty |
| Warranty Details | Included Surge Suppressor comes with a lifetime limited warranty and \$100,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only). Charging Station has a 1-year limited warranty. |
| CATEGORY PAGE FILTERS (Y/N ONLY) | |
| External Receptacle | No |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.