

Industrial Locking Charging Station for 32 Zebra devices, industrial handhelds, or smartphones - USB with Syncing

MODEL NUMBER: CSD32USBIND



Provides fast charging, convenient syncing, secure storage and device organization for up to 32 Zebra devices, industrial handhelds, or smartphones in an industrial environment.

Features

Fast Charging for Up to 32 Industrial Handhelds

The CSD32USBIND features 32 USB-A ports that deliver up to 2.4A apiece to charge Zebra devices, industrial handhelds, smartphones, or other devices with USB charging. It stores up to 32 devices with cases up to 7 x 3.65 x 1 inches. For larger devices, there are two large 7.19 x 17.24 x 19.5 inch shelves. Individual shelf dividers and numbered ports keep the devices organized. This lockable charging station is designed for industrial spaces, such as factory floors, warehouses and construction areas, but is also ideal for corporate, healthcare, commercial and retail environments.

Convenient Syncing

A USB uplink port connects to a host computer for wired syncing to update software, back up data and return devices to standard configurations. The CSD32USBIND also supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing).

Locking Steel Enclosure Keeps Mobile Devices Safe and Secure

This secure charging station promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. A three-point locking mechanism with included keys helps prevent device theft, damage and tampering. An optional padlock hasp (with a user-supplied padlock) provides added security. Flow-through ventilation helps protect against overheating, and attachment points on the top and bottom of the CSD32USBIND allow mounting of cooling fans (sold separately). Specially coated shelves help prevent device scratches and scuffs.

Firmware Upgrade Ports for Software Upgrades

Mini-USB firmware upgrade ports enable future software upgrades to support newer devices.

Easy to Install

This lockable charging station ships ready for quick, easy installation. The split front doors open 180 degrees for improved device and service access. Rear-panel slots support wall-mount installation, while the unit is also set up for easy desktop securing. If you need to charge more than 32 devices at once, a second CSD32USBIND can be stacked on top of the first one to avoid taking up additional surface space. For convenient power connections, you can choose which side to attach the power cord.

Highlights

- Built to endure industrial settings, such as factories, warehouses and construction sites
- USB-A ports support 2.4A of fast charging of up to 32 Zebra devices, smartphones, or other USB devices
- Uplinks to host computer for updating software, backing up data and other syncing
- Stores devices in a locking steel enclosure designed to keep phones safe and secure
- 10 ft. AC input cord with right-angle 5-15P plug allows flexible placing near wall outlet

Package Includes

- CSD32USBIND 32-Device USB Charging Station
- Padlock hasp
- Detachable AC input cord (10 ft./3 m) with right-angle NEMA 5-15P plug
- (2) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Specifications

OVERVIEW	
UPC Code	037332282477
Charging Form Factor	Stationary Cabinet
Product Type	Multi-Device Charger
Charger Functions	Charge; Secure; Sync
Device Compatibility	Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
OUTPUT	
Frequency Compatibility	50 / 60 Hz
POWER	
Power Consumption (Watts)	112.00
CHARGING	
Number of Charging Ports	32
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	Black
Charging Station Form Factor	Stationary Cabinet
Shipping Dimensions (hwd / in.)	21.26 x 21.26 x 26.38



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	54.00 x 54.00 x 67.01
Shipping Weight (lbs.)	77.29
Shipping Weight (kg)	35.06
Slot Dimensions (hwd / in.)	3.67 x 1.0 x 7.0
Unit Dimensions (hwd / in.)	18.560 x 23.630 x 18.190
Number of Shelves	2
Assembly Required	No
ENVIRONMENTAL	
Operating Temperature Range	32° to 86°F (0° to 30°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	5% to 95% RH (Non-Condensing)
FEATURES & SPECIFICATIONS	
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
STANDARDS & COMPLIANCE	
Product Certifications	UL 60950-1
Product Compliance	FCC (USA); FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.