

## Datashield Serial In-Line Surge Protector, DB9

MODEL NUMBER: DB9



Is your DB9 serial connection protected? If not, your equipment is vulnerable to damage and performance problems. Surges and line noise don't just affect the power line; they can enter your equipment on any connection. So protect your DB9 serial equipment with the DataShield™ DB9 In-Line Surge Suppressor. It's the ideal choice for protecting PCs, printers, modems and anything with a DB9 connection.

### Description

Tripp Lite's DB9 offers dataline surge suppression for DB9 serial ports of data terminal and data communications equipment, including PCs, printers, modems and more. User configurable for use with male or female captive DB9 ports. Offers protection on all 9 lines, plus D shell chassis. Convenient DB9 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges, faulty wiring or lightning away from network interface connections. Tripp Lite network surge suppressors reduce blown interface cards, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground. SUPPRESSION: Reversible DB9 m/f jacks, protects pins 1-9 and chassis, 18V clamping

### Features

- DB9 protects 9 pin serial connections for dataline surge suppression of data terminal, data communications equipment and PCs, printers, modems and more
- Reversible for use with male or female captive DB9 ports
- Offers protection on all 9 data lines, plus D shell chassis
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

## Specifications

OVERVIEW	
UPC Code	037332010834

### Highlights

- Complete serial port (DB9) surge protection
- Protects against the effects of electrostatic discharge, faulty wiring and lightning

### Package Includes

- 1 DB9 Surge Suppressor



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>OUTPUT</b>	
Output Receptacles	(1) Network
Circuit Breaker (amps)	340
Right-Angle Outlets	No
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Right-Angle Plug	No
Integrated Cord Clip	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	18
Auto Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	1-9 & Chassis
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	5.00 x 3.00 x 2.00
Shipping Dimensions (hwd / cm)	12.70 x 7.62 x 5.08
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.07
Integrated Keyhole Mounting Slots	No
Color	Light Gray
Anti-Microbial Protected	No
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>