

350W Power Inverter/Charger for Mobile Medical Equipment, 120V - IEC 60601-1, Remote User Interface

MODEL NUMBER: HC350SR



Medical inverter/charger with IEC 60601-1 powers equipment used in healthcare facilities inside and outside patient care areas.

Features

350W 120V Medical-Grade Mobile Power Inverter/Charger for Medical Carts This cost-effective hospital-cart power inverter/charger for medical equipment integrates seamlessly into your existing system. The HC350SR medical inverter battery charger is the ideal solution for providing safe, compliant power to mobile medical equipment used both inside and outside patient care areas. It is compatible with SLA batteries (not included).

Medical Inverter Provides IEC 60601-1 Compliance for All Connected Electronic Devices An isolation transformer reduces the cumulative shock potential of connected equipment, which helps ensure IEC 60601-1 compliance for use in every sector of healthcare facilities, including patient care areas. In addition to IEC 60601-1, this module meets NFPA, NEC and Joint Commission standards.

Smart Charging System for Long Battery Life The advanced three-stage charger recharges batteries faster and more safely than conventional chargers. An internal automatic transfer switch (ATS) lets the module power connected equipment while also recharging the battery at the same time. The HC350SR can provide multiple hours of AC power in standard configuration, though runtime varies depending on battery condition and load.

Combats Electromagnetic Interference That Can Harm Equipment Various electromagnetic and radio sources found in virtually every medical facility can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems and can lead to incremental hardware damage and data corruption. The HC350SR incorporates technology that filters out disruptive line noise so it won't affect your equipment.

Superior Design for Simple Fuss-Free Use The HC350SR's simple cart and fleet management lets you track usage data at a glance. Tripp Lite's free downloadable PowerAlert software automatically saves valuable patient data from loss or corruption if the cart is left unattended and battery power is depleted. An included remote user interface displays output and battery status and features on/off and alarm-mute switches.

Rugged Construction Sure to Stand Up to Demanding Environments The compact steel housing features a USB communication port and one C13 AC outlet on a six-inch dangle for connecting a device's power cord. It is designed to endure in severe medical environments where reliable power is essential.

Specifications

Highlights

- All-in-one inverter/charger/controller powers equipment on mobile medical carts
- IEC 60601-1 compliance for use inside and outside patient care areas
- Approved to EN60601-1-2:2015, 4th Ed.
- Included remote user interface (RUI) displays output and battery charge status
- Internal ATS powers connected equipment and recharges battery simultaneously
- Free PowerAlert® software protects valuable patient data from loss or corruption

Applications

- Power a computer, monitor, USB hub, barcode scanner or other equipment on a mobile medical cart used inside or outside patient care areas

Package Includes

- HC350SR 350W Power Inverter/Charger for Mobile Medical Equipment, 120V
- Remote user interface



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332127341
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	IEC
Voltage Compatibility (VAC)	120
Voltage Compatibility (VDC)	12
Input Phase	Single-Phase
Input Cord Length (ft.)	0.5
Input Cord Length (m)	0.15
OUTPUT	
Frequency Compatibility	60 Hz
Pure Sine Wave Output	Yes
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(1) C13
Continuous Output Capacity (Watts)	150
Peak Output Capacity (Watts)	225
Individually Controllable Load Banks	No
BATTERY	
Expandable Battery Runtime	Yes
DC System Voltage (VDC)	12
Full Load Runtime	Up to 6 hours typical runtime in standard configuration. Runtime varies depending on battery condition and load
Battery Charge	Equal to discharge time. Includes advanced 3-stage (9-20A) battery charger
Expandable Runtime	Yes
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	On Remote User Interface (RUI): Output AC Power, Battery Charge Level and Battery Charging Status (Sold Separately)
Switches	On Remote User Interface (RUI): On/Off Switch and Alarm-Mute Switch (Sold Separately)
Audible Alarm	Low Battery Alarm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Material of Construction	Steel
Primary Form Factor	Tower
Shipping Dimensions (hwd / in.)	7.40 x 8.80 x 13.90
Shipping Weight (kg)	7.35
Unit Dimensions (hwd / cm)	29.2 x 15.2 x 8.9
Unit Dimensions (hwd / in.)	11.5 x 6 x 3.5
Unit Weight (kg)	6.35
Unit Weight (lbs.)	14
COMMUNICATIONS	
Network Monitoring Port	USB
Communications Interface	USB
STANDARDS & COMPLIANCE	
Certifications	Tested, certified and compliant to IEC60601-1, CAN/CSA-C22.2 No. 601.1-M90 and UL 1778 by TUV
UPS Certifications	UPS Certifications Tested to IEC60601-1 (medical grade)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Optional Coverage	<u>WEXT1E</u> - 1 year extended warranty <u>WEXT2E</u> - 2 year extended warranty <u>WEXT3E</u> - 3 year extended warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>