


Dual Full-Motion Desk Mount for 13" to 26" Flat-Screen Displays

MODEL NUMBER: DDR1323SD



Description

Tripp Lite's VESA-compliant DDR1323SD Dual Flat-Screen Desk Stand frees up valuable space in your workstation and increases workday productivity by enabling the suspension of 2 flat-panel displays on a single base. It features convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 26-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware, and each mount supports weights of up to 30 lbs. For peace of mind, the DDR1323SD comes backed by a 5-year warranty.

Features

- Tripp Lite's VESA-compliant DDR1323SD Dual Flat-Screen Desk Stand frees up valuable space in your workstation and increases workday productivity by enabling the suspension of 2 flat-panel displays on a single base
- Convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 26-inch flat-panel displays
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware, and each mount supports weights of up to 30 lbs
- 5-year warranty

Specifications

OVERVIEW	
UPC Code	037332178756
PHYSICAL	
Color	Black; Silver

Highlights

- **SEE NEW MODEL - DDR1326SD**
- Increases available desk/table space in office workstation applications
- Dual mounts fit most flat-panel displays from 13" to 26"
- Convenient one-touch display adjustment for easy view optimization and improved ergonomics
- Wide range of motion with -15° to +15° tilt, 180° swivel and 360° rotation capability
- Each mount supports up to 30 lbs.
- 5-year warranty

Package Includes

- DDR1323SD Full-Motion Flat-Screen Desk Mount
- Mounting Hardware
- Owner's Manual



Powering Business Worldwide



Material of Construction	Metal
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Maximum Weight Capacity (lbs.)	30
Maximum Weight Capacity (kg)	14
Shipping Dimensions (hwd / in.)	5.91 x 13.39 x 25.87
Shipping Dimensions (hwd / cm)	15.01 x 34.01 x 65.71
Shipping Weight (lbs.)	11.70
Shipping Weight (kg)	5.31
Unit Dimensions (hwd / in.)	14.760 x 28.030 x 11.810
Unit Weight (lbs.)	11.55
Unit Weight (kg)	5.24
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.