

## Internet Office 120V 500VA 280W Standby UPS, USB port, 6 Outlets, Tel/DSL/Ethernet Protection

MODEL NUMBER: INTERNETOFFICE500



### Highlights

- 500VA tower 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- INTERNETOFFICE500 UPS System
- USB cable
- Phone cable
- Instruction manual

### Description

Tripp Lite's INTERNETOFFICE500 standby UPS system offers surge suppression and long-lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Internal UPS circuits support entry-level PC systems for up to 30 minutes during power failures and brownouts so that connected equipment can be shut down without data loss. Offers complete desktop power protection in an attractive gray tower configuration. Includes 3 battery-supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in case of extended power failure; cable included. PowerAlert software available via FREE download. Built-in TEL/DSL or ethernet line surge suppression protects connected equipment from damaging surges. Built-in audible alarm and 3 front-panel LEDs indicate line power status, battery power status and battery low/replace status. 500VA/280W power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Offers 4.6 min. battery runtime with a full load of 500VA and 14.8 min. with a half load of 250VA. Supports user battery replacement via built-in access panel. \$150,000 connected equipment insurance (USA, Puerto Rico, & Canada only).

### Features

- INTERNETOFFICE500 standby UPS system offers UPS battery support, plus complete AC and tel/Ethernet modem line surge suppression
- Supports entry level PC systems for up to 30 min. during brownouts and power failures, enabling safe system shutdown
- Supports a max load of 500VA/280W for 4.6 min.
- Supports a half load of 250VA/140W for 14.8 min.
- Supplies battery-derived AC output during brownouts starting at 99V and overvoltages starting at 147V; user adjustment allows fine tuning of brownout response to any setting from 83V to 99V
- Attractive gray tower configuration
- Includes 3 battery-supported outlets, 3 surge suppression-only outlets and 6-ft. AC line cord (all NEMA 5-15)



Powering Business Worldwide



- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [tripplite.eaton.com/products/power-alert](http://tripplite.eaton.com/products/power-alert)
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Dateline suppression jacks protect a single dialup phone/DSL line or network Ethernet line connection
- Audible alarm and 3 front-panel LEDs indicate line power, battery power and battery low/replace status
- 500VA/280W power handling ability supports a variety of computer, internetworking, telecom and consumer electronics equipment
- Supports user battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Compatible with 120V/60Hz applications for USA, Canada, Mexico and more
- \$150,000 connected equipment insurance (USA, Puerto Rico, & Canada only)

## Specifications

OVERVIEW	
UPC Code	037332032706
UPS Type	Standby
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
OUTPUT	
Output Capacity (VA)	500
Output Capacity (Watts)	280
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave



Powering Business Worldwide



Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Runtime Full Load (min.)	4.6 min. (280w)
Runtime Half Load (min.)	14.8 min. (140w)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	<a href="https://tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	3 LEDs indicate line power, battery power and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	480
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount ( <a href="https://tripplite.eaton.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems~UPSWM">UPSWM</a> - tower mounting kit)
Primary UPS Depth (mm)	178
Primary UPS Height (mm)	216



Powering Business Worldwide

**TRIPP-LITE**  
by **EATON**

Primary UPS Width (mm)	132
Shipping Dimensions (hwd / in.)	9.25 x 8.10 x 11.90
Shipping Dimensions (hwd / cm)	23.50 x 20.57 x 30.23
Shipping Weight (lbs.)	13.40
Shipping Weight (kg)	6.08
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	21.59 x 13.21 x 17.78
UPS Power Module Dimensions (hwd, in.)	8.5 x 5.2 x 7
UPS Power Module Weight (kg)	6.35
UPS Power Module Weight (lbs.)	14
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	68
AC Mode Efficiency Rating (100% Load)	94%
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="https://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">https://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>
Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99V (adjustable to 83V via potentiometer)
High Voltage Transfer to Battery Power (Setpoint)	176 (adjustable to 147 via potentiometer)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS

APPLICATIONS	
UPS Applications	Computer/Peripherals
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.