

## 14-Outlet Economy Network Server Surge Protector, 1U Rack-Mount, 15-ft. Cord, 3000 Joules

MODEL NUMBER: DRS-1215



### Highlights

- 14 outlets / 15-ft. cord
- 3000 joule rating
- Adjustable rackmount hardware

### Package Includes

- DRS-1215 Surge Suppressor
- Warranty information
- Instruction manual

### Description

Tripp Lite's DRS-1215 offers surge and noise suppression in a versatile all-metal multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch EIA standard rack. Includes 14 outlets (6 front/8 rear), 15 ft AC power cord and guarded power switch to reduce the risk of accidental shutoff. Diagnostic LED indicates surge protection status.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 14 NEMA5-15R (6 front & 8 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping/3000 joules

FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

### Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- 3000 joules AC surge suppression with EMI/RFI filtering
- 14 NEMA 5-15R output receptacles (6 front/8 rear)
- 15 foot AC cord with NEMA 5-15P straight-in plug connection
- Diagnostic LED confirms suppressor operation
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15 amp capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility



## Specifications

OVERVIEW	
UPC Code	037332100245
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(14) 5-15R
Circuit Breaker (amps)	15
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Power switch controls power to all outlets
Diagnostic LED Details	Green - Protection Present
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3000
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V



EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
Auto Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	9.30 x 2.50 x 20.40
Shipping Dimensions (hwd / cm)	23.62 x 6.35 x 51.82
Shipping Weight (lbs.)	5.50
Shipping Weight (kg)	2.49
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 10.16
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Material of Construction	Metal
Included Mounting Accessories	Included mounting flanges are pre-installed for 1U rackmount installation and can be re-configured to support a variety of mounting options
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Color	Black
Form Factors Supported	1U rackmount, 0U vertical rackmount, wallmount and under-counter mounting supported - detachable flanges can be re-configured to support a variety of additional mounting options
Outlets Measurement (Center to Center)	Distance between front outlets = 38.9mm; Distance between rear outlets = 38.9mm
Anti-Microbial Protected	No
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
Canada	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>