

DataShield In-Line Surge Protector for Network and Digital/Leased Lines, T-1, ISDN, 1-Set RJ11/45/48

MODEL NUMBER: DSUT1CSU



What do you currently have protecting your high-speed RJ45 connection? If the answer is nothing, your equipment is in danger of being damaged by surges and line noise. Even with protection on your power line, you are still vulnerable to these power problems on your network connection. Use the DataShield™ DSUT1CSU Network Surge Suppressor to protect your network. It's ideal for sensitive "U" and "S/T" interfaces on modems, NT1 devices, CSU/DSUs, terminal adapters and other pieces of high-speed equipment.

Description

Tripp Lite's DSUT1CSU offers complete surge suppression for equipment on digital and leased lines, T1 and ISDN interfaces. Ideal for the protection of sensitive "U" and "S/T" interfaces on modems, NT1 devices, CSU/DSUs, terminal adapters and other pieces of high-speed equipment. Convenient 8 position input/output RJ style jacks are RJ11/45/48 compatible, includes 5 inch ethernet patch cable for convenient placement at the protected device network connection. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges, faulty wiring or lightning away from network interface connections. Tripp Lite network surge suppressors reduce blown interface ports, garbled network transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

SUPPRESSION: 1 set RJ11/45/48 in/out jacks, protects wires 1-8, 60V clamping

Features

- DSUT1CSU offers full surge suppression for CSU/DSU's and other high speed equipment on digital and leased lines, T1 and ISDN interfaces
- Convenient RJ45 input and output connections make for simple installation (RJ45 input/output connections, pins 1-8, 60V clamping)
- 5 inch ethernet patch cable enables ideal protection placed as close as possible to the point of use
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

Highlights

- Complete T1 and ISDN (RJ11/45/48) surge protection
- Protects against the effects of electrostatic discharge, faulty wiring and lightning

Package Includes

- DSUT1CSU dataline protector
- 5 inch RJ45 patch cable
- Instruction manual and warranty information



Specifications

OVERVIEW	
UPC Code	037332010872
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Plug Type	RJ45
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	200
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	60
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
Additional Dataline Protection	1-8
PHYSICAL	
Antimicrobial Coating	No
Color	Light Gray
Integrated Keyhole Mounting Slots	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	15.49 x 5.08 x 7.87
Shipping Dimensions (hwd / in.)	6.10 x 2.00 x 3.10
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
COMMUNICATIONS	
Network Speed	10/100 Mbps
SPECIAL FEATURES	
Rotatable Outlets	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>