


# Fixed TV Wall Mount for 26" to 70" Displays

MODEL NUMBER: DWF2670X



Mounts a flat- or curved-screen television or monitor on the wall in your classroom, conference room, restaurant, lobby or home theater.

## Features

### Mounts Your TV or Monitor on the Wall for a Perfect Viewing Angle

Recommended for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this low-profile TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat- and curved-panel displays from 26 to 70 inches and up to 165 pounds (75 kilograms).

### Durable All-Metal Construction Provides Convenient Cable Access

The fixed TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Its open frame design with smooth edges enables easy access to cables. Horizontal mounting rails adjust to compensate for off-center wall studs. A built-in bubble level helps ensure your display is evenly mounted. Removing and replacing the display is fast and simple using the automatic spring locks with quick-release cords.

### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 50 x 50, 75 x 75, 100 x 100, 100 x 150, 100 x 200, 150 x 100, 150 x 150, 200 x 100, 200 x 200, 200 x 400, 300 x 200, 300 x 300, 350 x 350, 400 x 200, 400 x 300 and 400 x 400. Mounting hardware is included.

## Highlights

- Accepts most popular flat- and curved-screen displays from 26 to 70 in. up to 165 lb.
- Automatic spring locks with quick-release cords ensures quick and easy display removal
- Adjustable horizontal mounting rails help compensate for off-center wall studs
- Open architecture and built-in level enable easy cable access and accurate leveling
- Conforms to current VESA standards to ensure compatibility with your display

## System Requirements

Supports VESA mounting hole patterns 50 x 50, 75 x 75, 100 x 100, 100 x 150, 100 x 200, 150 x 100, 150 x 150, 200 x 100, 200 x 200, 200 x 400, 300 x 200, 300 x 300, 350 x 350, 400 x 200, 400 x 300 and 400 x 400

## Package Includes

- DWF2670X Fixed TV Wall Mount
- Mounting hardware
- Owner's manual

# Specifications

OVERVIEW	
UPC Code	037332266095
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel



Powering Business Worldwide



VESA Pattern (mm)	50x50; 75x75; 100x100; 100x150; 100x200; 200x100; 200x200; 200x400; 300x200; 300x300; 350x350; 400x200; 400x300; 400x400
Motion	Fixed
Mounting Location	Wall
Degrees of Motion	Fixed
Distance from Wall (in.)	1.1
Distance from Wall (cm)	3
Distance from Wall (mm)	28
Minimum Screen Size (in.)	26
Minimum Screen Size (cm)	66.04
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Number of Displays	1
Unit Dimensions (hwd / in.)	16.500 x 17.240 x 1.100
Unit Dimensions (hwd / cm)	42.0 x 43.79 x 2.79
Unit Weight (lbs.)	2.3
Unit Weight (kg)	1.04
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; RoHS3; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.