

Heavy-Duty Full-Motion Security TV Wall Mount for 37" to 80", Flat or Curved, UL Certified

MODEL NUMBER: DWMSC3780MUL



Security wall mount with combination lock hangs your flat-panel or curved-screen television or monitor.

Features

Security Wall Mount Hangs Your Flat-Panel or Curved-Screen TV or Monitor Ideal for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this heavy-duty TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel or curved-screen displays from 37 to 80 inches and up to 88 pounds. Mounting hardware is included.

Durable All-Metal Construction Provides Convenient Cable Access The curved-TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. This heavy-duty wall mount is function- and weight-tested to 200 pounds in accordance with UL Standard 2442.

Designed to Keep Your Display Safe and Secure This security wall mount was conceived with your television or monitor's safety in mind, especially if the display is located in a public area with much unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included four-position combination lock.

Tilt and Swivel Features Let You Adjust the Viewing Angle to Your Specifications The full-motion TV wall mount allows adjustment of your display's horizontal angle from -10° to $+5^{\circ}$. It also swivels your monitor or television 90° left to right. This will minimize glare on the screen and allow you to customize the angle for comfortable viewing.

Complies with VESA Standards VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This heavy-duty wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 300 x 200, 300 x 300, 300 x 400, 300 x 500, 300 x 600, 300 x 700, 300 x 800, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300, 600 x 400, 700 x 300, 700 x 400, 800 x 300 and 800 x 400.

Highlights

- Accepts most popular flat- or curved-screen displays from 37 to 80 in. up to 88 lb.
- Function- and weight-tested in accordance with UL Standard 2442 up to 200 lb.
- Solid steel security bar and included combo lock deter tampering and theft
- Open architecture and built-in level enable easy cable access and accurate leveling
- Tilts -10° to $+5^{\circ}$, swivels 90° to provide comfortable custom viewing angles

Applications

- Mounting a flat- or curved-screen television or monitor in an office lobby, conference room, bar, restaurant, airport or anywhere else digital signage is desired
- Securing an expensive display in a hotel lobby, classroom, library, hospital, truck stop or other public area with much foot traffic

Package Includes

- Wall plate
- (2) Adapter brackets
- Security bar
- Wall plate level
- (2) End caps
- (4) End cap screws
- (2) Anti-skid blocks
- (4) M5 x 14 screws



- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Large spacers
- (5) Anchor bolts
- (5) Concrete anchors
- (5) 20 mm washers
- Combination lock
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332225061
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Degrees of Motion	-10/+5 Tilt; 90 Swivel
Material of Construction	Steel
Maximum Screen Size (cm)	203.2
Maximum Screen Size (in.)	80
Maximum Weight Capacity (kg)	91
Maximum Weight Capacity (lbs.)	200
Minimum Screen Size (cm)	93.98
Minimum Screen Size (in.)	37
Motion	Full
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	100.08 x 33.53 x 6.86
Shipping Dimensions (hwd / in.)	39.40 x 13.20 x 2.70
Shipping Weight (kg)	10.70



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	23.60
Unit Dimensions (hwd / cm)	54.86 x 98.55 x 43.94
Unit Dimensions (hwd / in.)	21.6 x 38.8 x 17.3
Unit Weight (kg)	9.98
Unit Weight (lbs.)	22
VESA Pattern (mm)	300x200; 300x300; 300x400; 300x500; 300x600; 300x700; 300x800; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400; 700x300; 700x400; 800x300; 800x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	Yes
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>