

# 1000VA 1000W Line Conditioner - Automatic voltage regulation with surge protection

MODEL NUMBER: LS1006M



### Highlights

- Automatically adjusts low or high voltage
- 1000 watts continuous
- 6 NEMA 5-15R outlets
- **This product is available for purchase in Mexico only.**

### Package Includes

- LS1006M Line Conditioner
- Warranty information
- Instruction manual

### Description

The LS1006M automatic voltage regulation system offers complete protection from brownouts, overvoltages and transient surges for computers, printers, fax machines and more. Transformer-based voltage correction circuits maintain usable 120V nominal AC output during brownouts as low as 93V and overvoltages to 141V. Network grade equipment protection offers AC surge and noise suppression rated at 720 joules. Single telephone line surge suppression protects modem, fax machine, cordless phones and other devices with a dialup/DSL line connection. Supports loads up to 1000 watts. Includes six NEMA 5-15R outlets, six-foot line cord and three diagnostic LEDs that display boost, trim and normal regulation operation.

### Features

- Maintains usable 120V nominal output during brownouts as low as 93V and overvoltages as high as 141V
- 1000 watts output power rating supports 120V loads up to 8.3 amps
- Network grade surge suppression rated at 720 joules
- EMI/RFI noise filtering
- 3 diagnostic LEDs indicate boost, trim and normal LC operation
- 6 protected NEMA5-15R outlets
- 6-ft. AC power cord with standard NEMA5-15P input plug
- Single line surge suppression protects modem, fax machine and other system peripherals with a phone line connection from damage due to surges on phone/DSL lines

## Specifications

OVERVIEW	
UPC Code	037332116239
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide

TRIPP LITE  
SERIES

Maximum Input Amps / Watts	1250 watts / 8.3 amps
Maximum Input Amps	9
Maximum Input Watts	1056
Input Plug Features	Straight Plug
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (Watts)	1000
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(6) 5-15R
Output Nominal Voltage	120V
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Maintains usable 120V nominal output to sensitive electronics during severe brownouts and overvoltages.
Overvoltage Correction	Input voltages over 128V (+/-3V) are reduced by 10.6%
Undervoltage Correction	Input voltages between 111V (+/-3V) and 103V (+/-3V) are boosted by 13.4%.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LEDs	3 LEDs (Boost, Trim, Normal)
<b>SURGE / NOISE SUPPRESSION</b>	
EMI / RFI AC Noise Suppression	20 dB
AC Suppression Joule Rating	720
<b>PHYSICAL</b>	
Material of Construction	Plastic
Form Factors Supported	Small Tower
Housing Color	Gray
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	7.25 x 5.75 x 7.00
Shipping Dimensions (hwd / cm)	18.42 x 14.60 x 17.78
Shipping Weight (lbs.)	7.00
Shipping Weight (kg)	3.18



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / in.)	5.500 x 4.750 x 4.750
Unit Dimensions (hwd / cm)	13.5 x 12 x 11.5
Unit Weight (lbs.)	6
Unit Weight (kg)	2.72
<b>FEATURES &amp; SPECIFICATIONS</b>	
Additional Information	Single line telephone / DSL line surge suppression jacks
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; NOM (Mexico); UL 1012; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 & <a href="https://tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.