

# Safe-IT USB-A to Lightning Sync/Charge Antibacterial Cable (M/M), MFi Certified, White, 3 m (9.8 ft.)

MODEL NUMBER: M100AB-03M-WH



USB/Lightning cable with antibacterial properties connects your Apple iPhone, iPad or iPod to the USB-A port on your computer or wall/car charger.

## Features

### USB Cable Charges and Syncs Your Latest-Generation iPhone, iPad and iPod

This Safe-IT™ sync/charge cable (M/M) connects your iPhone, iPad or iPod to the USB-A port on a computer, laptop, car charger or wall charger. It allows you to charge and power your Apple device, while simultaneously syncing and transferring photos, MP3s and other important files at USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

### Antibacterial Properties Provide Extra Protection

The molded connectors and PVC jacket are constructed using an antibacterial material that is effective in inhibiting the growth of Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

### MFi-Certified for Broad Device Compatibility

The 5V 2.4A (12W max) Lightning cable is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

### Reversible Lightning Connector Attaches in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible 8-pin Lightning male connector plugs into an Apple device's port in either direction for an instant connection every time.

## Specifications

| OVERVIEW   |                                 |
|------------|---------------------------------|
| UPC Code   | 037332261052                    |
| Technology | Lightning; USB 2.0 (High Speed) |

## Highlights

- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Made with antibacterial material proven effective in inhibiting the growth of E. coli and staph
- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable data transfers
- Reversible Lightning plug connects in either direction for immediate no-fuss use

## Applications

- Charge and sync your Apple iPhone, iPad or iPod using the USB port on your computer or a wall charger up to 3 meters away
- Transfer photos and other important files between an external hard drive and your Apple device
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

## System Requirements

- Computer, laptop or charger with USB-A port
- Most current iPhone, iPad and iPod devices

## Package Includes

M100AB-03M-WH USB-A to Lightning Sync/Charge Antibacterial Cable (M/M), White, 3 m (9.8 ft.)



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                       |                                     |
|---------------------------------------|-------------------------------------|
| Cable Type                            | Passive                             |
| <b>CONNECTIONS</b>                    |                                     |
| Side A - Connector 1                  | USB A (MALE)                        |
| Side B - Connector 1                  | LIGHTNING (MALE)                    |
| Connector Plating                     | Nickel                              |
| Contact Plating                       | Gold                                |
| Connector Style                       | Straight                            |
| <b>PHYSICAL</b>                       |                                     |
| Material of Construction              | PVC                                 |
| Cable Jacket Color                    | White                               |
| Cable Jacket Material                 | PVC                                 |
| Cable Jacket Rating                   | VW-1                                |
| Cable Outer Diameter (OD)             | 4.6mm                               |
| Cable Length (ft.)                    | 9.8                                 |
| Cable Length (m)                      | 2.99                                |
| Cable Length (in.)                    | 118.1                               |
| Shipping Dimensions (hwd / in.)       | 1.40 x 2.50 x 6.10                  |
| Shipping Weight (kg)                  | 0.16                                |
| <b>ENVIRONMENTAL</b>                  |                                     |
| Operating Temperature Range           | 32° to 113°F (0° to 45°C)           |
| Storage Temperature Range             | -40° to 158°F (-40° to 70°C)        |
| Operating Humidity Range              | 10% to 85% RH, Non-Condensing       |
| Storage Humidity Range                | 5% to 90% RH, Non-Condensing        |
| Power Provided to Connected Device(s) | 12W (5V/2.4A)                       |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |                                     |
| Antimicrobial                         | No                                  |
| USB Specification                     | USB 2.0 (up to 480 Mbps)            |
| Antibacterial                         | Yes                                 |
| <b>STANDARDS &amp; COMPLIANCE</b>     |                                     |
| Product Certifications                | MFi                                 |
| Product Compliance                    | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY &amp; SUPPORT</b>         |                                     |



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                         |
|--|-------------------------|
| Product Warranty Period<br>(Worldwide) | 2-year limited warranty |
|--|-------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.