



Powering Business Worldwide

9PX G2 Maintenance Bypass for Select 8kVA to 11kVA 9PX UPS Systems, Hardwired Input/Output, 4 L6-30R Outlets, 0U Rack/Tower/Wall

MODEL NUMBER: MBP11K208G2



Reroutes utility power to keep essential equipment operational while you're servicing or replacing a UPS system.

Features

Compatible with Select Eaton 8kVA/11kVA 9PX G2 UPS Systems

The MBP11K208G2 works with Eaton's 9PX8KG2, 9PX8KTF5G2, 9PX11KG2, 9PX11KTF11G2 and 9PX11KTF5G2 UPS systems. The bypass switch lets you service or replace the UPS system without powering down any equipment and risking costly downtime. Power passes directly from a power source to equipment when in bypass mode.

Versatile Connection and Installation Options

The MBP11K208G2 features hardwired input and output connections, as well as four NEMA L6-30R outlets. You can mount the maintenance bypass to the rear of the UPS or extended battery module (EBM) without taking up additional rack space. You can also mount the bypass on the side or top of the rack, on a wall or adapt it for tower installation using the included hardware.

Specifications

OVERVIEW	
UPC Code	786689876074
Accessory Type	Bypass Panel (Rack-Mount)
Accessory Class	UPS Accessories
INPUT	
UPS Input Connection Type	Hardwire
Input Plug Type	Hard-wire

Highlights

- Isolates UPS from connected loads for maintenance without powering down equipment
- Designed for 0U rear rack mounting, tower or wall mounting using the included hardware
- Compatible with Eaton's 8kVA to 11kVA 9PX G2 UPS systems

System Requirements

Compatible with Eaton's 9PX8KG2, 9PX8KTF5G2, 9PX11KG2, 9PX11KTF11G2 and 9PX11KTF5G2 UPS systems

Package Includes

- MBP11K208G2 Maintenance Bypass
- (2) Input/output covers
- Input/output cover fixation kit
- (2) Conduits for UPS input/output connection
- (4) Conduit fittings
- Mounting hardware



Powering Business Worldwide

OUTPUT	
Output Capacity (VA)	11000
Output Capacity (kVA)	11
Output Capacity (Watts)	11000
Output Capacity (kW)	11
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	208V; 220V; 230V; 240V
Output Receptacles	(4) L6-30R
Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	0U
Unit Dimensions (hwd / in.)	5.120 x 11.220 x 5.120
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.