





Powering Business Worldwide

Universal-Input Metered PDU G4, 208V and 415/240V, 24 Outlets, Input Cable Sold Separately, 0U Vertical

MODEL NUMBER: EVMIGU23A-E



Metered-input UPDU with removable input cable (sold separately) accommodates both single- and three-phase power in 208V and 415/240V environments.

Features

17 Removable Power Cables with 15 Different Plugs Support Universal Input

This universal-input PDU (UPDU) G4 is designed to meet your most diverse rack-power needs. Fully metered with 24 outlets and sophisticated management capabilities, the EVMIGU23A-E accommodates power needs ranging from 5kVA single-phase to 23kVA three-phase. Pair the UPDU with one of 17 removable power cables with 15 different plug options (all sold separately). By delivering a broad range of power options, this UPDU alleviates the cost and complexity of mixing and matching different PDUs for different installations. It also ensures you won't outgrow your PDU as your power needs evolve.

Market-Leading Cybersecurity Ensures Your Data Is Kept Safe

Chain-of-trust encryption and secure firmware boot capability prevent the EVMIGU23A-E UPDU from being a cyberattack vulnerability point on a network. An embedded, hot-swappable gigabit network module (GNM) offers enhanced management and cybersecurity, including zero-trust architecture and zero-touch provisioning. The EVMIGU23A-E is compatible with select Eaton Brightlayer Data Centers suite software solutions that enable extensive automation and remote management to shorten response times to power issues and ensure timely updates for stronger cybersecurity.

Remote Management Saves Time and Money

The GNM with multi-color screen supports performance management software for real-time reports, trend charts, dashboards and alerts that are prioritized by severity, as well as remote troubleshooting and automated responses during power events. The EVMIGU23A-E is compatible with optional environmental sensors (sold separately) that provide alerts about temperature, humidity and dry-contact device connections.

24 Outlets Give You Plenty of Power Options

The EVMIGU23A-E rack PDU (rPDU) features 12 C13 outlets, which accept C14 connectors, and 12 high-retention C39 combo outlets, which accept both C14 and C20 connectors, adding flexibility to deployments and reducing the quantity of PDUs you will need to purchase and install.

Convenient Box-to-Rack Installation

This UPDU G4 features toolless mounting buttons that allow front- or side-facing rack installation, depending on your rack's layout and your power needs. Choose from a collection of 17 power cables and 15 plug options (all power cables sold separately). Low-profile circuit breakers are flush with the

Highlights

- Universal power input accommodates 5kVA single-phase to 23kVA 3-phase levels
- Allows choice of 17 power cables and 15 plug options to customize your application
- 24 outlets include 12 C13 and 12 universal C39, which accepts C14 and C20 plugs
- Embedded Gigabit Network Module offers market-leading cybersecurity
- Toolless mounting buttons allow 0U vertical installation in your 32U or higher rack

Package Includes

EVMIGU23A-E Universal-Input Metered Rack PDU G4



Powering Business Worldwide

lightweight aluminum chassis, and the narrow two-inch width saves space within the rack for revenue-generating equipment. You can cascade up to 40 EVMIGU23A-E models with each model maintaining its own individual IP address from a single network connection point.

Specifications

OVERVIEW	
UPC Code	786689812447
PDU Type	Metered
INPUT	
Input Phase	3-Phase; Single-Phase
PDU Input Voltage	200-415V
Maximum Input Amps	55.0
Input Connection Type	Universal Input
PDU Plug Type	Hardwire
Input Cord Length Details	0
Voltage Compatibility (VAC)	1-Phase; 208; 230; 3-Phase; 415
Input Plug Type	Universal
Input Cord Details	Universal Input
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
OUTPUT	
Output Capacity (kVA)	23
Output Capacity (Watts)	23000
Output Capacity (kW)	23
Output Capacity Details	5-23kW (208-415V) total capacity; 60A max per output phase
Frequency Compatibility	50 / 60 Hz
Output Receptacle Details	(12) C13; (12) C39 combo outlets
Output Circuit Breakers	(6) 2-pole 20A circuit breakers
Nominal Output Voltage(s) Supported	100V; 110V; 120V; 200V; 208V; 230V; 240V; 415V
Output Receptacles	(12) C13; (12) C39
Output Nominal Voltage	100V; 110V; 120V; 200V; 208V; 230V; 240V; 415V
Overload Protection	(6) 2-pole 20A circuit breakers
CONNECTIONS	
Ethernet Interface	Yes



Powering Business Worldwide

Serial Interface	Yes
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Cascade up to 40 PDUs
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	LCD pixel display with section readings and automatic shut-off to save energy. Set IP address, rotate display, view alarms and read current, voltage, power and energy.
LED Indicators	Green = outlet is on; Red = PDU has power but outlet is off
Current Measurement Accuracy (Amps)	+/-1%
Voltage Measurement Accuracy (Volts)	+/-1%
Power Measurement Accuracy (Watts)	+/-1%
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Aluminum
Rack Height	0U
Form Factors Supported	Vertical
Housing Color	Black
Included Mounting Accessories	Mounting buttons
Included Mounting Accessory Description	Factory-installed shoulder-style aluminum mounting buttons. 49" center-to-center Alternative flush-style mounting buttons also included with PDU.
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	67.78 x 4.65 x 5.40
Shipping Dimensions (hwd / cm)	172.16 x 11.81 x 13.72
Shipping Weight (lbs.)	9.93
Shipping Weight (kg)	4.50
Unit Dimensions (hwd / in.)	55.900 x 2.050 x 2.560
Unit Dimensions (hwd / cm)	141.98 x 5.08 x 6.50
Unit Weight (lbs.)	8
Unit Weight (kg)	3.63
Rack Units	32
Mounting Details	Mounting Buttons
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)



Powering Business Worldwide

COMMUNICATIONS	
Network Monitoring Port Description	Eaton Gigabit Network Module G4
Network Monitoring Port	Serial/Ethernet ports for environmental monitoring and daisy-chain connections
SNMP Compatibility	Yes
Network Compatibility	10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit); 1000 Mbps
FEATURES & SPECIFICATIONS	
High Availability PDU Features	Advanced cybersecurity
STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); UL 62368-1; cTUVus
Product Compliance	FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.