


7-Outlet Home/Business Theater Surge Protector, 6-ft. Cord, 2100 Joules, Tel/Modem/Coax Protection

MODEL NUMBER: HT706TSAT



Highlights

- 7 outlets / 6 ft. cord
- 2100 joule rating
- 2-line 2.2 GHz gold coaxial surge protection
- 1-line tel/modem surge protection

Package Includes

- HT706TSAT Home/Business Theater Surge Suppressor
- 6 ft. gold coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information

Description

Tripp Lite's HT706TSAT Home/Business Theater Surge Suppressor provides high-performance protection--2100 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 7 outlets (with transformer spacing), 2-line 2.2 GHz coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$100,000 Ultimate Lifetime Insurance coverage (U.S., Canada, and Puerto Rico only). Includes two diagnostic LEDs, 6 ft. cord with a right-angle plug, 6 ft. coaxial cable and 6 ft. phone cord.

Features

- 2100 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected components against surge damage...for life!
- 7 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 4 transformers
- 2 sets of surge-protected 2.2 GHz gold coaxial connectors (with included 6 ft. gold coaxial cable)
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line
- 6 ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status



- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Integrated circuit breaker protects against dangerous system overload
- High-impact plastic housing (black) stands up to the most demanding environments
- UL and CSA listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332121486
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Right-Angle Outlets	Yes
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	75000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch



Diagnostic LED Details	Built-in LEDs confirm protection and grounding status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2100
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400, 400, 500
EMI / RFI Filtering	Up to 40 dB
Auto Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	2 line
Network (Ethernet) Protection	No
PHYSICAL	
Anti-Microbial Protected	No
Color	Black
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	160mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between transformer outlet and standard outlet = 38.10mm; Distance between standard outlets = 25.40mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	64.01 x 36.07 x 15.24
Shipping Dimensions (hwd / in.)	25.20 x 14.20 x 6.00
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Unit Dimensions (hwd / cm)	3.81 x 35.56 x 8.26
Unit Dimensions (hwd / in.)	1.5 x 14 x 3.25
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.2



CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Canada	CSA
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>