

Isobar 6-Outlet Surge Protector, 6 ft. Cord with Right-Angle Plug, 3330 Joules, Diagnostic LEDs, Tel/Coax/Modem, Metal

MODEL NUMBER: ISOBAR6DBS



Premium protection for A/V home theater components, including HDTVs and stereo receivers, against dangerous power surges, spikes and line noise. Recommended for professional-grade home theater installations.

Description

Premium protection for your expensive home theater and computer equipment, the ISOBAR6DBS Isobar® 6-Outlet Surge Protector features a network-grade surge protection rating of 3330 joules to defend your sensitive electronics against even the strongest surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$250,000 for life (valid in the U.S., Canada and Puerto Rico only).

The ISOBAR6DBS features six NEMA 5-15R outlets, which are arranged in three exclusive isolated filter banks that prevent equipment connected to one bank from interacting with equipment connected to the other. These internal barriers also prevent disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems. Coaxial and RJ11 jacks also protect your incoming cable, satellite and telephone/DSL signals.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the ISOBAR6DBS protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Included safety covers protect against dust while blocking accidental contact with unused outlets. An integrated 12A circuit breaker protects all outlets and shuts down connected equipment in the event of an overload. A lighted on/off switch provides one-touch control over connected components. Diagnostic LEDs

Highlights

- 6 NEMA 5-15R outlets in exclusive isolated filter banks
- Network-grade 3330-joule surge protection rating
- 2-line 2.2 GHz gold coaxial protection
- Coaxial cable/telephone line/modem surge protection
- 6 ft. AC power cord with right-angle NEMA 5-15P plug

Package Includes

- ISOBAR6DBS Isobar 6-Outlet Surge Protector, Tel/Coax/Modem, Metal Housing
- Gold coaxial cable, 6 ft.
- RJ11 telephone cable, 6 ft.
- (4) Outlet safety covers
- Owner's manual



show power, protection and line fault status at a glance. A six-foot power cord with right-angle 5-15P plug reaches nearby outlets and allows furniture to be placed flush against the wall.

Features

Network-Grade 3330-Joule Surge Protection for Your Home or Work Electronics Protects your A/V components, network hardware, retail displays, appliances, power tools and other expensive electronics against even the strongest surges and spikes Recommended for network workstations, telecom systems, point-of-sale equipment and A/V systems requiring AC line protection Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression Exceeds IEEE 587 Category A and B surge suppression specifications Coaxial and RJ11 jacks protect cable, satellite and telephone/DSL signals

6 Outlets Accept Wide Range of Electronic Devices 6 NEMA 5-15R AC outlets accept most computer equipment, electronics and appliances Outlets accommodate up to 3 bulky transformers without blocking other outlets Included safety covers block accidental contact with unused outlets

Isolated Filter Banks Provide Extra Protection Outlets arranged in 3 exclusive isolated filter banks to limit noise interaction among connected equipment Block disruptive EMI/RFI line noise up to 80 dB that can cause equipment damage or data loss Combine large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

Premium Safety Features Lighted on/off switch provides one-touch control over connected equipment Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Diagnostic LEDs confirm power, protection and line fault status at a glance Conforms to current UL 1449 3rd Edition safety standards

Fits Effortlessly Into Your Setup 6 ft. AC power cord reaches nearby outlets Space-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wall Keyhole slots on bottom panel provide convenient wall or desk mounting options Metal housing designed for long life

Backed by Tripp Lite's Ultimate Lifetime Insurance \$250,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332011213
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	135000
Input Plug Type	NEMA 5-15P



Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and two position red illuminated on/off power switch
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3330
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	40-80 dB
Isolated Filter Banks	3
Auto Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	2 line
Network (Ethernet) Protection	No
PHYSICAL	
Anti-Microbial Protected	No
Color	Black
Color (AC Line Cord)	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 210.79mm; Distance between vertical tabs = 58.17mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 39.45mm; Distance between vertical outlets = 39.30mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	Black
Shipping Dimensions (hwd / cm)	31.24 x 7.37 x 18.80
Shipping Dimensions (hwd / in.)	12.30 x 2.90 x 7.40
Shipping Weight (kg)	1.63
Shipping Weight (lbs.)	3.60
Unit Dimensions (hwd / cm)	6.35 x 22.9 x 8.9
Unit Dimensions (hwd / in.)	2.5 x 9 x 3.5
Unit Weight (kg)	1.27
Unit Weight (lbs.)	2.8
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC PFCC Part 68art 68
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>