

## Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M) - Blue, 5 ft. (1.52 m)

MODEL NUMBER: **N001-005-BL**



### Description

Tripp Lite's 5-ft. (1.52 m) blue snagless category 5e (Cat5e) patch cable has 2 snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Standard category 5e patch cables are also available.

### Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 5-ft. (1.52 m) color: blue connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available - Cat6 cables (N201 series)

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332099921 |

### Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

### System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

### Package Includes

- 5-ft. (1.52 m) Blue Snagless Cat5e Patch Cable



|                                 |                      |
|---------------------------------|----------------------|
| Technology                      | Cat5/5e              |
| <b>PHYSICAL</b>                 |                      |
| Color                           | Blue                 |
| Cable Shielding                 | UTP                  |
| Cable Jacket Material           | PVC                  |
| Cable Jacket Rating             | CM                   |
| Number of Conductors            | 4 Pair               |
| Cable Outer Diameter (OD)       | 5.0mm                |
| Conductor Material              | Stranded Copper      |
| Conductor Gauge                 | 26 AWG               |
| Cable Length (ft.)              | 5                    |
| Cable Length (m)                | 1.5                  |
| Cable Length (in.)              | 60                   |
| Cable Length (cm)               | 152.4                |
| Shipping Dimensions (hwd / cm)  | 22.86 x 17.78 x 1.27 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50   |
| Shipping Weight (kg)            | 0.06                 |
| Shipping Weight (lbs.)          | 0.13                 |
| <b>COMMUNICATIONS</b>           |                      |
| Bandwidth per TIA Standard      | 100 MHz              |
| Maximum Bandwidth as Tested     | 350 MHz              |
| Network Speed                   | 1Gbps                |
| <b>CONNECTIONS</b>              |                      |
| Side A - Connector 1            | RJ45 (MALE)          |
| Side B - Connector 1            | RJ45 (MALE)          |
| Crossover Wiring                | No                   |
| Contact Plating                 | Gold                 |
| Connector Type                  | Molded; Snagless     |
| Wiring Configuration            | EIA/TIA 568B         |
| <b>SPECIAL FEATURES</b>         |                      |
| IP68 Rated                      | No                   |
| Antibacterial                   | No                   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
|-------------------------------------|---------------------------|
| Certifications                      | RoHS, REACH               |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>