

## Cat5e Retractable (UTP) Ethernet Cable (RJ45 M/M) - Black, 4 ft. (1.22 m)

MODEL NUMBER: **N009-004-R**

### Highlights

- Ideal for connecting the RJ45 network port on your notebook to a network
- Cables extend easily and retract automatically

### System Requirements

- PC/Notebook with RJ45 Ethernet Port
- Network Jack with RJ45 Ethernet Port

### Package Includes

- 4-ft. (1.22 m) Retractable RJ45 M/M Cable for Laptop Ethernet Port

### Description

Tired of carrying all those loose cords around? When you're an on-the-go business person with no time to spare, who wants to carry all those loose laptop cords with you while traveling? Eliminate all those worries with the retractable RJ45 Ethernet Patch Cable. It fits easily in your notebook case or pocket and extends up to 4-ft. (1.22 m) in length and gracefully retracts into a small reel. RJ45 male to male connectors.

### Features

- Automatic spring retractable cord
- Great alternative to carrying loose network cables
- Ethernet 802.3 compliant

## Specifications

OVERVIEW	
UPC Code	037332131706
Technology	Cat5/5e
POWER	
Power Over Cable (PoC) Support	No
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Contact Plating	Gold



Powering Business Worldwide

TRIPP LITE  
SERIES

Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
Angled Connector	No
<b>PHYSICAL</b>	
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Shielding	UTP
Cable Outer Diameter (OD)	0.5*8.0mm
Conductor Material	Stranded Copper
Conductor Gauge	32 AWG
Cable Length (ft.)	4
Cable Length (m)	1.22
Cable Length (in.)	51.2
Cable Length (cm)	121.9
Shipping Dimensions (hwd / in.)	0.25 x 0.25 x 1.00
Shipping Dimensions (hwd / cm)	0.64 x 0.64 x 2.54
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 104°F (-10° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Bandwidth per TIA Standard	100 MHz
Maximum Bandwidth as Tested	350 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3ab
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
IP20 Rated	No



Powering Business Worldwide

TRIPP LITE  
SERIES

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; IEEE 802.3ab 1000Base-T; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.