


## Cat5e 350 MHz Bulk Solid-Core PVC Cable, Black, 1000 ft., TAA

MODEL NUMBER: N022-01K-BK



Premium cabling designed for Cat5/5e premise (in-wall) applications, such as connecting an Ethernet wall jack to a router, patch panel or switch.

### Description

The N022-01K-BK Cat5e 350 MHz Bulk Solid-Core PVC Cable is premium cabling designed for Cat5/5e premise applications, such as connecting an Ethernet wall jack to a router, patch panel or switch. Designed for fast transmission and excellent signal quality, this black cable ensures peak performance through your LAN (local area network).

Manufactured from 24 AWG copper wire, the four-pair solid UTP N022-01K-BK delivers speeds up to 350 MHz/1 Gbps. Protected by a CMR-rated PVC jacket, this cable is ideal for all non-plenum horizontal wiring applications, including 10/100/1000 Base-T Ethernet, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.

The N022-01K-BK meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e, draft 11).

### Features

#### Perfect Solution for Cat5/5e Premise Applications

- Designed for fast transmission and excellent signal quality throughout your LAN
- Delivers speeds up to 350 MHz/1 Gbps
- Ideal for all non-plenum horizontal wiring applications, including 10/100/1000 Base-T Ethernet, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications

#### Premium Construction for Superior Performance

- Made from 24 AWG copper wire

### Highlights

- Ideal for all non-plenum horizontal wiring applications
- Rated for 350 MHz/1 Gbps communications
- High-quality 24 AWG 4-pair solid copper wire
- CMR-rated PVC jacket
- Meets IEEE 802.3ab and ANSI/EIA/TIA 568 standards

### Package Includes

- N022-01K-BK Cat5e 350 MHz Bulk Solid-Core PVC Cable, Black, 1000 ft.



- 4-pair solid UTP
- CMR-rated PVC jacket
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e, draft 11)

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332144195
INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.8
Cable Length (in.)	12000
Cable Length (cm)	30480
PHYSICAL	
Cable Jacket Rating	CMR
Cable Shielding	UTP
Color	Black
Shipping Dimensions (hwd / cm)	27.00 x 35.00 x 35.00
Shipping Dimensions (hwd / in.)	10.63 x 13.78 x 13.78
Shipping Weight (kg)	9.07
Shipping Weight (lbs.)	20.00
Snagless Connector	No
Wire Gauge (AWG)	24
Wire Type	Solid
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	Cat5/5e
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>