

4U Hinged Wall-Mount Patch Panel Bracket, TAA

MODEL NUMBER: **N060-004**



Description

Tripp Lite's heavy duty 14-gauge steel, 4U (7.0") wall mount patch panel bracket, is the ideal alternative to a full size rack. Standard EIA 19-inch width allows installation of any 19inch patch panel. Laser cut metal (not punched) keeps all edges smooth, greatly reducing the possibility of injury, and, wear on cable jackets. Universal mounting for right or left hinging. Keyholes are spaced 16inches for mounting on wall studs. Stamped, horizontal reinforcement ribs allow for greater sturdiness and stability, and allow the addition of a rear cutout for feeding cable through a wall opening. Smooth, glossy black finish.

Features

- 4U height (7.0"), 6inch depth
- Laser cut for smooth edges
- 16 -inch center mounting
- Universal left or right hinge mounting
- Rear cut-out for through the wall cabling
- Standard EIA 19inch width accepts any manufacturers EIA compliant patch panel
- Smooth, black glossy finish
- Heavy duty 14 gauge steel with stamped reinforcement ribs

Specifications

OVERVIEW	
UPC Code	037332126405
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	13.97

Highlights

- Laser cut 14-gauge steel results in smooth edges
- Keyholes on 16-inch centers plus through-the-wall cabling cut-out
- Accepts any standard 19inch Patch Panels
- 4U Height (7.0"): 19"wide x 7.0" high x 6.0" deep
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 4U Wallmount Patch Panel Bracket
- Pkg 10 mounting screws



Maximum Device Depth (in.)	5.5
Maximum Device Depth (mm)	140
Rack Height	4U
Shipping Dimensions (hwd / cm)	16.51 x 52.07 x 19.05
Shipping Dimensions (hwd / in.)	6.50 x 20.50 x 7.50
Shipping Weight (kg)	2.59
Shipping Weight (lbs.)	5.70
Unit Dimensions (hwd / cm)	17.78 x 48.26 x 15.24
Unit Dimensions (hwd / in.)	7 x 19 x 6
Unit Weight (kg)	2.27
Unit Weight (lbs.)	5
Weight Capacity - Stationary (kg)	16
Weight Capacity - Stationary (lbs.)	35
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS, UL 60950
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>