

## 3-Port Metal DIN-Rail Mounting Module for Snap-In Keystone Jacks and Couplers, Silver, TAA

MODEL NUMBER: N063-003



Accepts snap-in keystone jacks and couplers to help you manage your DIN-rail network cable application.

### Features

#### Organizes a Wide Variety of Ethernet Network Patch Cables in Your DIN-Rail Installation

This DIN-rail mounting module lets you manage network cable interconnectivity with three blank cutouts, which accommodate all snap-in keystone jacks and in-line couplers. Made from sheet metal with nickel plating, the N063-003 is quick and easy to install on a standard 35-millimeter DIN rail using the built-in mounting clip.

#### TAA-Compliant for GSA Schedule Purchases

The N063-003 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Heavy-duty metal construction ideal for industrial Ethernet network applications
- 3 blank cutouts compatible with all keystone jacks and couplers
- Built-in mounting clip attaches to standard 35 mm DIN rail with no tools needed
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

N063-003 Metal DIN-Rail Mounting Module, 3 Ports

## Specifications

OVERVIEW	
UPC Code	037332276889
Technology	Cat5/5e; Cat6; Cat6a
Firmware / Software Docs	
Offset Ports	No
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	(3) KEYSTONE JACK CUTOUT
PHYSICAL	
Primary Form Factor	DIN-Rail



Powering Business Worldwide

TRIPP LITE  
SERIES

Color	Silver
Material of Construction	SUS304 & SPCC NI PLATE (STEEL)
Total Number of Ports	3
Shipping Dimensions (hwd / in.)	2.10 x 4.50 x 8.00
Shipping Weight (lbs.)	0.15
Unit Dimensions (hwd / in.)	2.120 x 1.940 x 2.380
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-13° to 122°F (-25° to 50°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	10% to 85% RH, (Non-Condensing)
<b>FEATURES &amp; SPECIFICATIONS</b>	
All-in-One Kit	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Numbered Ports	No
DIN Mountable	Yes
Keystone Jacks	Yes
Built-in Cables	No
Color-Coded Connections	No
EIA/TIA 2/32 Spacing	No
Labeled Ports	No
Down-Angled Ports	No
Panel Applications	Ethernet
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); REACH; RoHS; UKCA; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.