



Powering Business Worldwide

250-ft. Gray Cat5e 350 MHz Molded Shielded Ethernet Cable

MODEL NUMBER: **N105-250-GY**

Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 250-ft. Category 5e (Cat5e) Gray Shielded Patch Cable. This cable features 2 x shielded RJ45 50-micron Gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 350MHz/1Gbps communication. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45 connectors w/50-micron gold-plated contacts
- 4-pair 24 AWG Stranded STP with drain wire
- Molded boot for extra strain relief and durability
- TSB 568B (AT&T 258A)Wiring
- TIA/EIA and UL Certified

Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain relief and durability

Package Includes

- 250-ft. Cat5e Gray Shielded Patch Cable

Specifications

OVERVIEW	
UPC Code	037332099112
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
PHYSICAL	
Color	Gray
Cable Shielding	STP
Cable Length (ft.)	250
Cable Length (m)	76.22
Shipping Weight (lbs.)	6.20
Shipping Weight (kg)	2.81
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.