

UK-Style 6C-Type Unloaded Shuttered Module, White, TAA

MODEL NUMBER: **N042U-WHM-S-6C**



British-style 6C-type module mounts within a compatible gang frame for terminating premise data (Ethernet) applications.

Features

U.K. Unloaded Shuttered Module Connects Data Cable Lines at the Wall

This 6C-type insert module combines with a compatible gang frame (sold separately) to complete an in-wall wiring application, such as Gigabit Ethernet (data). A Cat5e/6/6a keystone jack snaps easily into the cutout for quick cable connection.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This durable white module is shuttered to resist dust. It blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Highlights

- Ideal for completing a data (Gigabit Ethernet) in-wall wiring installation
- High-impact plastic construction designed to blend in with your home/office décor
- Shuttered to prevent dust and other debris from damaging cable connection

Package Includes

N042U-WHM-S-6C UK-Style 6C-Type Unloaded Shuttered Module, White

Specifications

OVERVIEW	
UPC Code	037332269560
Technology	Cat5/5e; Cat6; Cat6a
Country/Region	UK
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
PHYSICAL	
Color	White
Material of Construction	Spring: Stainless Steel; Faceplate: ABS



Powering Business Worldwide

TRIPP LITE
SERIES

Total Number of Ports	1
Unit Dimensions (hwd / in.)	1.510 x 0.980 x 0.590
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.