

## Cat6 Gigabit Molded (UTP) Ethernet Cable (RJ45 M/M), Yellow, 7 ft. (2.13 m)

MODEL NUMBER: N200-007-YW



Ideal for connecting high-speed network components, such as computers, printers, video game systems, Blu-ray™ players, copy machines, routers and modems, in a home or office Cat5/5e/6 application.

### Features

#### The Ideal Solution for All High-Speed Cat5/5e/6 Networking

- Connects high-speed network components, such as computers, printers, video game systems, Blu-ray players, copy machines, routers and modems
- Designed for 1000Base-T, 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, Token Ring Type 3 and EIA/TIA applications
- Recommended for home or office applications
- Provides high-speed connections up to 550 MHz/1 Gbps
- Flawless signal delivery with minimal near-end crosstalk levels

#### Premium Construction Ensures Error-Free Signal Transfer

- Manufactured from 24 AWG 4-pair stranded UTP with staggered-pin plug design
- Molded RJ45 connectors and gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)

## Specifications

### OVERVIEW

### Highlights

- Premium cabling for Cat5/5e/6 home/office network applications
- Rated for 550 MHz/1 Gbps communication
- 24 AWG 4-pair stranded UTP with PVC jacket
- Gold-plated copper contacts minimize data loss
- Integral strain relief protects connectors from stress and cracking

### Package Includes

- N200-007-YW Cat6 Gigabit Molded Patch Cable, Yellow, 7 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

UPC Code	037332201904
Technology	Cat6
<b>PHYSICAL</b>	
Color	Yellow
Cable Shielding	UTP
Cable Jacket Material	PVC
Cable Jacket Rating	CM
Number of Conductors	4 Pair
Cable Outer Diameter (OD)	6.0mm
Conductor Material	Stranded Copper
Conductor Gauge	24 AWG
Cable Length (ft.)	7
Cable Length (m)	2.1
Cable Length (in.)	84
Cable Length (cm)	213.4
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.21
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 104 F (-10 to 40 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Network Speed	1Gbps
IEEE Standards Supported	802.3an
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Contact Plating	Gold



Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
<b>SPECIAL FEATURES</b>	
IP68 Rated	No
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>