


Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 6-in. (15.24 cm)

MODEL NUMBER: N201-S6N-BL



Connects critical components, such as computers, network adapters, routers, servers, modems, hubs and switches, in Gigabit Ethernet networks. Slim design increases airflow in tight spaces.

Features

Ideal Solution for Your Cat6 Gigabit Ethernet Networking Needs

- Recommended for connecting computers, network adapters, routers, servers, modems, hubs and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to Cat6 Gigabit/1 Gbps

Special Slim Design

- More than 38% smaller in diameter than standard Cat6 cable
- Increases airflow in tight spaces
- Better flexibility for installing around corners and through cable management panels

Snagless RJ45 Male Connectors

- snagless boots prevent locking tabs from damage during installation

Premium Construction for Superior Performance

- Manufactured from 28 AWG 4-pair stranded UTP
- Gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket stands up to long-term use

Highlights

- Over 38% slimmer than standard Cat6 cables
- Easy to route through cable management panels
- Rated for Cat6 Gigabit/1 Gbps communications
- 28 AWG 4-pair stranded UTP with PVC jacket
- Snagless connectors prevent damaged tabs during installation

Package Includes

- N201-S6N-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (M/M), 6 in.



Specifications

OVERVIEW	
UPC Code	037332206534
Technology	Cat6
PHYSICAL	
Color	Blue
Cable Shielding	UTP
Cable Jacket Rating	CM
Conductor Material	Stranded Copper
Wire Gauge (OD - mm ²)	28
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.2
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.01
Shipping Weight (lbs.)	0.03
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded; Snagless
SPECIAL FEATURES	
Snagless Connector	Yes
STANDARDS & COMPLIANCE	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>