


Cat6 Gigabit Solid-Core Plenum-Rated UTP CMP PVC Bulk Ethernet Cable, Gray, 1000 ft. (304.8 m)

MODEL NUMBER: N224-01K-GY



Features

- Designed for premise (in-wall) cabling applications in air ducts and drop ceilings
- Premium cabling for category 6, category 5e and category 5 applications
- Color: Gray / Length: 1000-ft.
- 24 AWG 4-pair solid cable with Gray Plenum (CMP) jacket
- Deliver stable performance up to 550MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in PVC cable as well (N222-01K-GY and N222-01K-BL)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications-rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications: reduces cross-talk and return loss
- IEEE 802.3ab
- 1,000ft Box PLENUM (CMP) 4-pair Solid UTP
- Designed for premise (in-wall) cabling applications in air ducts and drop ceilings
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

Package Includes

- 1000-ft. Cat6 Gigabit Bulk 4PR Solid Plenum CMP Cable

Specifications

OVERVIEW	
UPC Code	037332117083
Technology	Cat6
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Gray
Cable Shielding	UTP
Cable Jacket Rating	CMP
Conductor Material	Solid Copper
Cable Length (ft.)	1000
Cable Length (m)	304.8
Cable Length (in.)	12000
Cable Length (cm)	30480
Shipping Dimensions (hwd / cm)	35.00 x 35.99 x 35.00
Shipping Dimensions (hwd / in.)	13.78 x 14.17 x 13.78
Shipping Weight (kg)	14.06
Shipping Weight (lbs.)	31.00
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
SPECIAL FEATURES	
Snagless Connector	No
STANDARDS & COMPLIANCE	
Approvals	EIA/TIA CAT6 TIA/EIA- 568-B-2.1, DRAFT 9 standards
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>