


24-Port Cat6a Shielded Patch Panel - 10 Gbps, STP, 110 Punch Down, RJ45, 1U, TAA

MODEL NUMBER: N252-024-6A-SH



Shielded patch panel manages and organizes Cat6a input/output cable connections in your high-density Gigabit Ethernet network.

Features

Shielded 24-Port Patch Panel for High-Speed Cat6a Network Cabling

Organize and manage your high-density Cat6a application without taking up too much valuable rack space. This shielded patch panel offers 24 fully shielded RJ45 ports with color-coded 110 punch-down slots that are terminated using a proper punch-down tool. Both the front and rear connectors are clearly numbered and labeled (for custom naming) to help you identify individual cable runs. The patch panel supports T568A and T568B wiring standards. It is fully rated for 10 Gbps data transfer speeds in your network application.

Condenses 24 Ports into Just 1U of Space in Your 19 in. Enclosure or Open Frame Rack

The UL-certified patch panel supports mounting in 1U of EIA-standard 19-inch racks using the included hardware, freeing up valuable rack space for other equipment. Included cable ties and grounding wire help organize your connections, cut down on cable clutter, take stress off the connectors and maintain stable performance.

TAA-Compliant for GSA Schedule Purchases

The N252-024-6A-SH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332266316
Product Type	Punchdown
Technology	Cat5/5e; Cat6; Cat6a
Firmware / Software Docs	

Highlights

- Rated for 10 Gbps speeds for managing network connections in Ethernet applications
- 24 RJ45 ports numbered, labeled and color-coded for convenient wiring and ID
- Supports EIA/TIA T568A/B wiring standards for 110 punch-down terminations
- Mounts easily into 1U of space in your 19 in. rack for immediate use
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

Connect security cameras, sensors, routers, computers, switches, wireless access points and other network devices in a high-speed Ethernet setup

Package Includes

- N252-024-6A-SH 24-Port Cat6a Shielded Patch Panel
- (24) Cable ties
- (4) Screws
- (4) Rubber washers
- (4) Square fasteners
- Grounding wire
- Installation guide



Offset Ports	No
PHYSICAL	
Material of Construction	Panel: SECC; Shielded Case: Stainless; Plastic Frame: ABS, UL94V-0; Jack Housing: PC, UL94V-0
Color	Black
Panel Connector Type	Shielded
Cable Management	Bracket
Rack Height	1U
Shipping Dimensions (hwd / in.)	2.50 x 4.10 x 19.50
Shipping Weight (lbs.)	3.80
Termination Type	110-type
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154.4 F (-40 to 68 C)
Operating Humidity Range	10% TO 90% RH, Non-Condensing
Storage Humidity Range	10% TO 90% RH, Non-Condensing
CONNECTIONS	
Ports	24
Side A - Connector 1	(24) RJ45 (FEMALE)
Side B - Connector 1	(24) 110 IDC
FEATURES & SPECIFICATIONS	
Keystone Jacks	Yes
All-in-One Kit	No
Down-Angled Ports	No
Built-in Cables	No
Color-Coded Connections	No
Numbered Ports	Yes
EIA/TIA 2/32 Spacing	No
Labeled Ports	Yes
Network Speed Support	10 Gbps
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH, UL



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>