

24-Port Cat6a Feed-Through Patch Panel - 4PPoE Compliant, 1U Rack-Mount, RJ45 Ethernet, White, TAA

MODEL NUMBER: N254-024-6A-WH



PoE++-compliant patch panel manages and organizes Cat6a data/power cable connections in your high-density network.

Features

24-Port Patch Panel Manages and Organizes High-Density Cat6a Network Cabling

This patch panel meets or exceeds Cat6a specifications to enable quick, easy cable patching. Just plug Cat6a cables into its 24 front and rear RJ45 feed-through ports. No punch-down termination is required. Both the front and rear connectors are clearly numbered, and the front ports have blank labels to help you identify individual cable runs. The N252-P24-WH supports EIA/TIA 568A and 568B wiring standards and is compatible with all network applications. It is fully rated for fast Ethernet data transfer speeds up to 10 Gbps.

Designed for Use in Type 4 Power over Ethernet Plus (PoE++) Applications

The N254-024-6A-WH maximizes performance with Type 4 PoE++ (4PPoE) applications in which you can power connected devices without the need for a secondary power supply. Because this Cat6a patch panel supports up to 100W PoE, it can help supply the power to operate compatible data, voice, security and audio/video PoE devices, such as security cameras, VoIP telephones and access control devices. A PoE installation saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. It also helps you install PoE devices in areas far away from AC outlets, such as poles or ceilings.

Mounts in 1U of Space in Your 19 in. Enclosure or Open Frame Rack

The low-profile patch panel supports mounting in 1U of space in EIA-standard 19-inch racks. A removable cable management bracket helps organize your connections, cut down on cord clutter and maintain stable performance.

TAA-Compliant for GSA Schedule Purchases

The N254-024-6A-WH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW

Highlights

- Supports Type 4 PoE++ with up to 100W of power delivery
- 24 RJ45 ports numbered and labeled to allow easy connection identification
- Fully rated for fast Ethernet data transfer speeds up to 10 Gbps
- Mounts easily into 1U of space in your EIA-standard 19 in. rack for immediate use
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- N254-024-6A-WH 24-Port Cat6a Feed-Through Patch Panel
- Cable management bracket
- Grounding wire
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332284792
Product Type	Feed-Through
Technology	Cat6a
CONNECTIONS	
Number of Ports	24
PoE Capability	100W (802.3bt)
PoE Power Budget (Watts)	30
Side A - Connector 1	(24) RJ45 (FEMALE)
Side B - Connector 1	(24) RJ45 (FEMALE)
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
PHYSICAL	
Color	White
Material of Construction	PANEL: SPCC, PLASTIC FRAME: ABS, UL94V-0
Rack Height	1U
Shipping Dimensions (hwd / in.)	2.76 x 19.69 x 2.91
Shipping Dimensions (hwd / cm)	7.01 x 50.01 x 7.39
Shipping Weight (lbs.)	2.03
Shipping Weight (kg)	0.92
Unit Dimensions (hwd / in.)	1.700 x 19.000 x 1.250
Rack Units	1
Panel Style	Feed-Through
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% TO 90% RH, NON-CONDENSING
Storage Humidity Range	10% TO 90% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Data Transfer Rate	10 Gbps
Recommended Category Cable	Cat6a
Labeled Ports	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1863; UL 94; UL Listed; cUL Listed
Product Compliance	CE (Europe); IEEE 802.3bt PoE++; Trade Agreements Act (TAA); UKCA



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.