

## Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Gray, 6 in.

MODEL NUMBER: N201-06N-GY



Connects critical components, such as computers, network adapters, routers, servers, modems, hubs and switches, in Gigabit Ethernet networks. Recommended for distributing data, voice and video in high-density data centers.

### Description

The N201-06N-GY Premium Cat6 Gigabit Snagless Molded UTP Patch Cable (M/M) is recommended for distributing data, voice and video through computers, network adapters, routers, servers, modems, hubs and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this cable ensures peak performance throughout your local area network (LAN). It reduces impedance and structural return loss compared to standard 100 MHz wire.

This six-inch gray cable is designed for 1000Base-T (1 Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, Token Ring Type 3 and EIA/TIA applications. Manufactured from 24 AWG four-pair stranded UTP with a rugged PVC jacket, the N201-06N-GY delivers speeds up to 550 MHz/1 Gbps and flawless signal delivery, while keeping near-end crosstalk levels to a minimum.

The RJ45 short-body connectors' snagless design protects the locking tabs from being damaged or broken off during installation. Corrosion-resistant gold-plated copper contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. Meets most other current industry standards, including IEEE 802.3ab, 802.5, ISO/IEC 11801 and ETL (Cat6 draft 11).

### Features

#### The Ideal Solution for Your Cat6 Gigabit Ethernet Networking Needs

- Recommended for connecting computers, network adapters, routers, servers, modems, hubs and switches in high-density data centers
- Designed for 10/100/1000 Base-T, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, Token Ring Type 3

### Highlights

- Premium cabling for Cat6 home/office network applications
- Rated for 550 MHz/1 Gbps communications
- Snagless connectors prevent damaged tabs during installation
- 24 AWG 4-pair stranded UTP with PVC jacket
- Integral strain relief protects connectors from stress and cracking

### Package Includes

- N201-06N-GY Premium Cat6 Gigabit Snagless Molded UTP Patch Cable (RJ45 M/M), Gray, 6 in.



and EIA/TIA applications

- Provides high-speed connections up to 550 MHz/1 Gbps
- Flawless signal delivery with minimal near-end crosstalk levels
- Reduces impedance and structural return loss compared to standard 100 MHz wire

#### Snagless RJ45 Male Connectors

- Molded snagless boots prevent locking tabs from damage during installation

#### Premium Construction Ensures Error-Free Signal Transfer

- Manufactured from 24 AWG 4-pair stranded UTP
- Gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket stands up to long-term use

#### Meets Top Cabling Standards

- Meets Cat6 TIA/EIA standards
- Meets most other current industry standards, including IEEE 802.3ab, 802.5, ISO/IEC 11801 and ETL  
(Cat6 draft 11)

## Specifications

| OVERVIEW                        |                      |
|---------------------------------|----------------------|
| UPC Code                        | 037332206473         |
| Technology                      | Cat6                 |
| INPUT                           |                      |
| Cable Length (ft.)              | 0.5                  |
| Cable Length (m)                | 0.2                  |
| Cable Length (in.)              | 6                    |
| Cable Length (cm)               | 15.2                 |
| PHYSICAL                        |                      |
| Cable Shielding                 | UTP                  |
| Color                           | Gray                 |
| Shipping Dimensions (hwd / cm)  | 22.86 x 17.78 x 1.27 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50   |
| Shipping Weight (kg)            | 0.02                 |
| Shipping Weight (lbs.)          | 0.05                 |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                                  |
|-------------------------------------|----------------------------------|
| Snagless Connector                  | Yes                              |
| Wire Gauge (OD - mm <sup>2</sup> )  | 24                               |
| Wire Type                           | Stranded                         |
| <b>COMMUNICATIONS</b>               |                                  |
| Network Speed                       | 1Gbps                            |
| <b>CONNECTIONS</b>                  |                                  |
| Side A - Connector 1                | RJ45 (MALE)                      |
| Side B - Connector 1                | RJ45 (MALE)                      |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                  |
| Certifications                      | ROHS                             |
| Approvals                           | EIA/TIA CAT6 TIA/EIA - 568-B-2.1 |
| <b>WARRANTY</b>                     |                                  |
| Product Warranty Period (Worldwide) | Lifetime limited warranty        |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>