

## Down-Angle Cat6 Gigabit Molded UTP Ethernet Cable (RJ45 Right-Angle Down M to RJ45 M), Blue, 5 ft. (1.52 m)

MODEL NUMBER: N204-005-BL-DN



### Highlights

- Space saving design
- Right Angle Down connector to Straight
- Cat6 Gigabit rated

### System Requirements

- Use with Cat6, Cat5e, cat5, or VoIP Networks

### Package Includes

- 5-ft. (1.52 m) Blue Cat6 Right Angle Down to Straight RJ45 - RJ45 Patch cable

### Features

- 5-ft. (1.52 m) Blue Cat6, Right Angle Down to Straight RJ45 - RJ45 Patch cable
- PVC 4 Pair Stranded Conductors, 24AWG
- Fully Molded Ends
- ETL Verified to TIA/EIA -56b-B
- 550Mhz Gigabit Speed rated

## Specifications

| OVERVIEW                  |                 |
|---------------------------|-----------------|
| UPC Code                  | 037332167545    |
| Technology                | Cat6            |
| PHYSICAL                  |                 |
| Cable Jacket Color        | Blue            |
| Cable Jacket Material     | PVC             |
| Cable Jacket Rating       | CM              |
| Cable Shielding           | UTP             |
| Cable Outer Diameter (OD) | 6.0 mm          |
| Number of Conductors      | 4 Pair          |
| Conductor Material        | Stranded Copper |

|                                      |                                 |
|--------------------------------------|---------------------------------|
| Conductor Gauge                      | 24 AWG                          |
| Cable Length (ft.)                   | 5                               |
| Cable Length (m)                     | 1.52                            |
| Cable Length (in.)                   | 60                              |
| Cable Length (cm)                    | 152.4                           |
| Shipping Dimensions (hwd / in.)      | 0.25 x 7.00 x 10.00             |
| Shipping Dimensions (hwd / cm)       | 0.64 x 17.78 x 25.40            |
| Shipping Weight (lbs.)               | 0.10                            |
| Shipping Weight (kg)                 | 0.05                            |
| <b>ENVIRONMENTAL</b>                 |                                 |
| Operating Temperature Range          | 14 to 122 F (-10 to 50 C)       |
| Storage Temperature Range            | 5 to 140 F (-15 to 60 C)        |
| Operating Humidity Range             | 0% to 90% RH, Non-Condensing    |
| Storage Humidity Range               | 0% to 90% RH, Non-Condensing    |
| <b>COMMUNICATIONS</b>                |                                 |
| Bandwidth per TIA Standard           | 250 MHz                         |
| Maximum Bandwidth as Tested          | 500 MHz                         |
| Network Compatibility                | 1 Gbps (Gigabit)                |
| IEEE Standards Supported             | 802.3an; 802.3at                |
| <b>CONNECTIONS</b>                   |                                 |
| Side A - Connector 1                 | RJ45 (MALE)                     |
| Side B - Connector 1                 | RJ45 (MALE) - DOWN ANGLE        |
| Crossover Wiring                     | No                              |
| Contact Plating                      | Gold                            |
| PoE Type                             | Type 2 PoE+ (30W, IEEE 802.3at) |
| Connector Type                       | Molded                          |
| Wiring Configuration                 | EIA/TIA 568B                    |
| Angled Connector                     | Yes                             |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                 |
| IP68 Rated                           | No                              |
| Snagless Connector                   | No                              |
| Antibacterial                        | No                              |

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

| STANDARDS & COMPLIANCE              |   |
|-------------------------------------|---|
| Product Certifications              | UL Listed; cUL Listed   |
| Product Compliance                  | CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA |
| WARRANTY & SUPPORT                  |   |
| Product Warranty Period (Worldwide) | Lifetime limited warranty   |

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.