


Right-Angle Cat6 Gigabit Molded UTP Ethernet Cable (RJ45 Right-Angle M to RJ45 M), Blue, 20 ft. (6.09 m)

MODEL NUMBER: N204-020-BL-RA



Cat6 cable connects Gigabit Ethernet network components like routers, servers, and switches in high-density data centers.

Features

Right-Angle Cat6 UTP Cable Connects Equipment in Data Centers and VoIP Networks This Cat6 Ethernet cable is ideal for connecting network components, such as printers, computers, copiers, routers, servers, modems and switches, in high-density data centers. Designed for fast transmission and excellent signal quality, this RJ45 cable ensures data transfer speeds up to 1 Gbps throughout your Gigabit Ethernet or VoIP network.

Right-Angle RJ45 End Makes Connecting and Disconnecting Easier One RJ45 connector is designed at a 90-degree right angle, which prevents excessive bending and reduces stress on the cable. This makes the space-saving cable easy to plug into patch panels, switches and other devices located in a confined area or behind a desk.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This long Ethernet cable features a blue PVC jacket and molded blue ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332252067
Technology	Cat6
PHYSICAL	
Cable Jacket Color	Blue
Cable Jacket Material	PVC

Highlights

- Cat6 Ethernet patch cable delivers fast transmission speeds up to 1 Gbps in your LAN
- Right-angle RJ45 connector is easy to plug into switch or panel pressed against a wall
- Designed for home or office 10/100/1000Base-T Gigabit Ethernet networks
- Color-coded blue for fast, easy identification in a crowded rack or workstation

Applications

- Build a Gigabit Ethernet or VoIP network through the connection of routers, modems, switches and servers in a high-density data center
- Connect a workstation computer to the company server to gain access to printers, scanners and copiers
- Combine with other Tripp Lite patch cables to set up a color-coded system in a crowded rack
- Create a connection in a tight space, such as a repurposed server room or behind furniture

Package Includes

- N204-020-BL-RA Right-Angle Cat6 Ethernet Cable - 20-ft. (6.09 m), M/M, Blue

Cable Jacket Rating	CM
Cable Shielding	UTP
Cable Outer Diameter (OD)	6.0 mm
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	24 AWG
Cable Length (ft.)	20
Cable Length (m)	6.10
Cable Length (in.)	240
Cable Length (cm)	609
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Relative Humidity	0% to 90% RH, Non-Condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3an; 802.3at
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE) - RIGHT ANGLE
Crossover Wiring	No
Contact Plating	Gold
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
Angled Connector	Yes
FEATURES & SPECIFICATIONS	
IP68 Rated	No
Snagless Connector	No

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.