

Cat6 Gigabit Crossover Molded UTP Ethernet Cable (RJ45 M/M), Gray, 10 ft.

MODEL NUMBER: N210-010-GY



Highlights

- Premium cabling for Category 6 applications—rated for 550 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

Package Includes

- 10-ft. Cat6 Gray Crossover Cable Molded 550MHz

Description

Tripp Lite's 10-ft. Gray Category 6 (Cat6) crossover molded cable has 2 standard RJ45 molded male connectors featuring integral strain relief. The cable is designed to connect hub-to-hub, PC-to-PC or Mac-to-Mac and is perfect in conjunction with 10/100/1000 base-t networks. Molded connectors are a different color to help identify this cable as a crossover cable and not a standard patch cable. Manufactured from PVC 4-pair stranded UTP and rated for 550MHz/1Gbps communication. Snagless Category 6 patch cables are also available. Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL.

Features

- Cabling for Category 6 (Cat6) applications
- Length: 10-ft. color: gray with green snagless connectors. Connectors: RJ45 male
- Length: 7-ft. color: gray with green snagless connectors. Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 550MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL

Specifications

OVERVIEW

UPC Code

037332124357



INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Cable Length (cm)	304.8
PHYSICAL	
Cable Shielding	UTP
Color	Gray
Shipping Dimensions (hwd / cm)	0.64 x 15.49 x 19.05
Shipping Dimensions (hwd / in.)	0.25 x 6.10 x 7.50
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Snagless Connector	Yes
Wire Type	Stranded
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Technology	Cat6
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>