


Cat6 Gigabit Bulk UTP Stranded 24 AWG CMR PVC Cable, Gray, 1000 ft. (304.8 m) TAA

MODEL NUMBER: N220-01K-GY



Highlights

- Less impedance and structural return loss than 100 MHz wire
- Channel-tested to 250 MHz/1 Gbps communications
- High-quality 24 AWG 4-pair stranded copper wire
- CMR-rated PVC jacket
- Meets IEEE 802.3ab and ANSI/EIA/TIA 568 standards

Package Includes

- N220-01K-GY Cat6 Gigabit Bulk Stranded 24 AWG CMR PVC Cable, Gray, 1000 ft.

Premium high-speed cabling designed for creating custom-length Cat6 patch cables.

Features

Perfect Solution for High-Speed Cat6 Premise Applications

- Designed for do-it-yourself custom patch cable assemblies
- Delivers speeds up to 250 MHz/1 Gbps
- No center spline and overall 0.22 in. diameter makes for easy RJ45 plug termination
- Reduces impedance and structural return loss compared to standard 100 MHz wire
- Ideal for 10/100/1000 Base-T Ethernet, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, EIA/TIA and Token Ring Type 3 applications

Premium Construction for Superior Performance

- Made from 24 AWG copper wire (7 x 32 AWG per conductor)
- 4-pair stranded UTP
- Minimum near-end crosstalk
- CMR-rated PVC jacket
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6, draft 11)

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| OVERVIEW | |
|-------------------------------------|---------------------------|
| UPC Code | 037332196606 |
| Technology | Cat6 |
| PHYSICAL | |
| Color | Gray |
| Cable Shielding | UTP |
| Cable Jacket Rating | CMR |
| Conductor Material | Stranded Copper |
| Cable Length (ft.) | 1000 |
| Cable Length (m) | 304.8 |
| Cable Length (in.) | 12000 |
| Cable Length (cm) | 30480 |
| Shipping Dimensions (hwd / cm) | 28.45 x 34.04 x 33.02 |
| Shipping Dimensions (hwd / in.) | 11.20 x 13.40 x 13.00 |
| Shipping Weight (kg) | 10.43 |
| Shipping Weight (lbs.) | 23.00 |
| COMMUNICATIONS | |
| Network Speed | 1Gbps |
| CONNECTIONS | |
| Side A - Connector 1 | BARE WIRE |
| Side B - Connector 1 | BARE WIRE |
| SPECIAL FEATURES | |
| Snagless Connector | No |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>