

Cisco-Compatible SFP-10G-SR-S SFP+ Transceiver - 10GBase-SR, DDM, Multimode LC, 850 nm, 300 m (984 ft.)

MODEL NUMBER: N286-10G-SR-S



Links a multimode Gigabit Ethernet network cable to a Cisco router, server or switch's SFP port.

Features

SFP+ Transceiver Designed for Connection to Your Cisco Network Switch or Server This SFP+ transceiver allows you to connect a 50/125 multimode fiber optic cable to a 10 Gbps network router, server or switch. It transmits data up to 300 meters (984 feet) and supports bi-directional Gigabit Ethernet communication up to 11.1 Gbps. The metal housing protects against electromagnetic interference (EMI) and excessive power dissipation.

Functionally Equivalent to Cisco SFP-10G-SR-S Transceiver Module The MSA-compliant N286-10G-SR-S functions just like the equivalent Cisco SFP-10G-SR-S transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the SFP-10G-SR-S.

Hot-Swappable for Installation Without Network Interruption This input/output device is fully hot-swappable, so you can install it without a potentially costly 10 Gbps network shutdown or device reboot. Just plug the SFP+ end of the transceiver into your Cisco network device. The other end has an LC duplex connector to link with multimode fiber optic cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring DDM support lets you keep track of various operating statuses in real time, including transceiver temperature, input and output power, and supply voltage.

S-Class Transceiver Highly Recommended for Enterprise Network This S-Class fiber transceiver module is ideal for enterprise network runs of shorter distances than other standard modules. The S-Class N286-10G-SR-S supports only Ethernet protocol and operates only within commercial temperature ranges (0 to 70°C).

Highlights

- SFP+ transceiver module 100% compatible with Cisco's equivalent module
- Provides 10 Gbps throughput up to 300 m (984 ft.) via multimode fiber cabling
- LC duplex female connector supports 10GBase-SR signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

Applications

- Install an additional LC duplex port on a Cisco router, server or switch for the purpose of connecting a multimode Gigabit Ethernet network cable

System Requirements

- Cisco or other compatible network router, server or switch

Package Includes

- N286-10G-SR-S Cisco-Compatible SFP-10G-SR-S SFP+ Transceiver
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332249265
Technology	Multimode



PHYSICAL	
Color	Silver
Unit Dimensions (hwd / in.)	0.49 x 2.3 x 0.55
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.064
ENVIRONMENTAL	
Operating Temperature Range	23 to 185°F (-5 to 85°C)
Storage Temperature Range	-40 to 185°F (-40 to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Wavelength	850nm
Brand Compatibility	Cisco
Optical Port	LC
Transmission Distance	300 m
Mode Type	Multimode
Multi-Source Agreement (MSA) Compliant	Yes
SPECIAL FEATURES	
Data Transfer Rate	10Gbps
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.triplite.com/products/product-certification-agencies>