

Cisco-Compatible QSFP-DD Transceiver - 400GBase-SR8, MPO/APC MMF, 400 Gbps, 850 nm, 100 m (328 ft.)

MODEL NUMBER: N286-400G-SR8-C



Connects a multimode Gigabit Ethernet fiber optic network cable to a Cisco switch or server's QSFP-DD port.

Features

QSFP-DD Transceiver for Connecting to Your Cisco Network Switch or Server

This QSFP-DD transceiver allows you to connect a multimode fiber optic cable to a 400 Gbps network router, server or switch. It transmits data up to 100 meters (328 feet) using an 850 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

Functionally Equivalent to Cisco 400GBASE-SR8 Transceiver Module

The MSA-compliant N286-400G-SR8-C functions just like the equivalent Cisco 400GBASE-SR8 transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the 400GBASE-SR8.

Hot-Swappable for Installation Without Network Interruption

This input/output device is fully hot-swappable, so you can install it without a potentially costly 400 Gbps network shutdown or device reboot. Just plug the QSFP-DD end of the transceiver into your Cisco network device. The other end has an MPO/APC connector to link with multimode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring

DDM support lets you keep track of operating information in real time, such as transceiver temperature, input and output power and supply voltage.

Highlights

- QSFP-DD transceiver module 100% compatible with Cisco's equivalent module
- Provides 400 Gbps throughput up to 100 m via multimode fiber cabling
- 16-strand MPO/APC connector supports 400GBase-SR8 signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

Package Includes

N286-400G-SR8-C QSFP-DD Transceiver

Specifications

OVERVIEW

UPC Code

037332284129

Brand Compatibility	Cisco
Technology	Fiber; Multimode
Optical Mode	OM4
Mode Type	Multimode
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.70 x 3.10 x 5.70
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.700 x 3.100 x 5.700
Unit Weight (lbs.)	0.1102
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
COMMUNICATIONS	
Maximum Data Rate	400 Gbps
Network Compatibility	400 Gbps
Wavelength	840nm; 850nm; 860nm
Transmission Distance	100 m
CONNECTIONS	
Side A - Connector 1	QSFP-DD
Side B - Connector 1	16-STRAND MTP/MPO (FEMALE)
Connector Material	Zinc Alloy
FEATURES & SPECIFICATIONS	
Data Transfer Rate	400 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Driver Required	No
Optical Port	MPO/MTP
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; IEC/EN 63000
Product Compliance	RoHS; CE (Europe); FCC Part 15 Class B (USA); UKCA

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------