

24-Port 1U Rack-Mount Cat6/Cat5 110 Patch Panel, 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N252-024



Highlights

- 19-in. rackmount ready, 1U height (1.75")
- EIA/TIA 2/32 spacing
- 110 type punchdown termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat6 Patch Panel 568B- 24 Port, 1U

Description

Category 6 Patch Panels offer you all the functionality and compatibility as any name brand. Each panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Cat6 connecting hardware specifications. Color coded for both EIA/TIA 568A and 568B installations. 24 ports ensure a wide range of plug-n-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs and the high-density 19-inch panel design will save you valuable space in on the rack.

UTP Cat6 22-24 AWG solid cable

Features

- Cat6
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Rack mountable on a 19 rack (1U of space)

Specifications

| OVERVIEW | |
|--------------|---------------|
| UPC Code | 037332120038 |
| Product Type | Rackmount |
| Technology | Cat5/5e; Cat6 |
| CONNECTIONS | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------------|
| Number of Ports | 24 |
| Side A - Connector 1 | 110 IDC |
| Side B - Connector 1 | RJ45 (FEMALE) |
| PoE Type | Type 2 PoE+ (30W, IEEE 802.3at) |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / in.) | 2.20 x 20.50 x 4.25 |
| Shipping Dimensions (hwd / cm) | 5.59 x 52.07 x 10.80 |
| Shipping Weight (lbs.) | 1.30 |
| Shipping Weight (kg) | 0.59 |
| Panel Style | Punchdown |
| STANDARDS & COMPLIANCE | |
| Product Compliance | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.