

## 24-Port 1U Rack-Mount Cat5e/6 Offset Feed-Through Patch Panel with Cable Management Bar, RJ45 Ethernet, TAA

MODEL NUMBER: N254-024-OF



Feed-through patch panel with staggered RJ45 jacks manages and organizes Cat5e/6 input and output cable connections and reduces crosstalk in your high-density 10 Gbps Ethernet network. No 110 punchdown termination required.

### Description

The N254-024-OF 24-Port 1U Rack-Mount Cat5e/6 Offset Feed-Through Patch Panel meets or exceeds Cat5e/6 specifications and works with USOC, T568A and T568B wiring to comply with industry standards. Its 24 RJ45 coupler jacks are staggered to prevent crosstalk and interference emanating from adjacent ports. Because any interference and line noise can slow down your network, reducing the risk by offsetting the RJ45 jacks in rows is of great importance.

No 110 punchdown termination is required. Just plug your Cat5e/6 cables into the 24 RJ45 coupler jacks on both sides of the panel. The detachable cable management bar keeps patch cables neat, tidy and efficiently organized on the back of the panel. Ports are clearly numbered and labeled to help you identify connections. Patch panel mounts easily into 1U of an EIA-standard 19-inch rack. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

IEC 60512-99-001 Compliant

PoE Certification Number: 2018-773

UTP Cat6 Patch Cord (Requires PoE cable if used in PoE setting)

### Features

#### Cat5e/6 Feed-Through Patch Panel Manages and Organizes High-Density Network Cabling

- Meets or exceeds Cat5e/6 specifications
- Works with USOC, T568A and T568B wiring to comply with industry standards

#### 24 RJ45 Coupler Jacks Staggered to Ward Off Interference

- Front and rear RJ45 jacks are offset to prevent crosstalk and interference emanating from adjacent ports
- Ports are numbered and labeled for easy connection identification
- Low-profile form factor requires no 110 punchdown termination

#### Cable Management Bar on Rear

- Detachable bar keeps patch cables neat, tidy and organized

### Highlights

- Staggered RJ45 jacks reduce crosstalk and interference
- Meets or exceeds Cat5e/6 specifications
- Cable management bar keeps patch cables organized
- No 110 punchdown termination required
- Mounts into 1U of EIA-standard 19 in. racks
- Qualified to IEEE 802.3bt Type 4 PoE for up to 100W of power delivery

### Package Includes

- N254-024-OF 24-Port 1U Rack-Mount Cat5e/6 Offset Feed-Through Patch Panel
- (24) N235-001-6A snap-in RJ45 couplers
- Detachable cable management bar
- Quick Start Guide



Powering Business Worldwide



**Quick, Easy Installation**

- Mounts into 1U of EIA-standard 19 in. racks

**TAA-Compliant for GSA Schedule Purchases**

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

## Specifications

OVERVIEW	
UPC Code	037332205230
Product Type	Rackmount
Technology	Cat5/5e; Cat6
CONNECTIONS	
Number of Ports	24
PoE Power Budget (Watts)	30
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Unit Dimensions (hwd / in.)	1.700 x 19.000 x 1.250
Panel Style	Feed-Through
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.