


## Cat6a 10G Certified Snagless Shielded STP Ethernet Cable (RJ45 M/M), PoE, Blue, 7 ft.

MODEL NUMBER: N262-007-BL



### Highlights

- 7-ft. Augmented Cat6 (CAT6a) Shielded (STP) Snagless Patch Cable, Blue
- 10Gbps Over Copper
- Each cable Fluke® Tested and Verified

### Package Includes

- 7-ft. Cat6a Blue Patch Cable

### Description

Tripp Lite's N262-007-BL 7-ft. Blue Augmented Cat6 (Cat6a) Shielded (STP) Snagless patch cable allows 10Gbps data transmission over 4-pair copper. Each Cat6a cable is individually tested and certified on Fluke® test equipment. Snag-free strain relief boot provides the most secure and accurate connections.

### Features

- 7-ft. Blue Cat6a Shielded (STP) Snagless Patch Cable - 10Gbps
- 100% FLUKE® tested and certified
- ETL/UL Verified
- Supports IEEE 802.3af and is DTE power compliant
- Backward compatible with all previous 10BaseT generations
- RJ45 plug improves NEXT performance to 650Mhz
- 26AWG, 4-Pair, Stranded PVC cable
- Compatible with T568A and T568B wiring
- Easy disconnect snagless hood
- PoE rated to four times the standard

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332188298 |
| Technology | Cat6a        |



| <b>INPUT</b>                        |                           |
|-------------------------------------|---------------------------|
| Cable Length (ft.)                  | 7                         |
| Cable Length (m)                    | 2.1                       |
| Cable Length (in.)                  | 84                        |
| Cable Length (cm)                   | 213.4                     |
| <b>PHYSICAL</b>                     |                           |
| Cable Shielding                     | STP                       |
| Color                               | Blue                      |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Weight (kg)                | 0.10                      |
| Shipping Weight (lbs.)              | 0.22                      |
| Snagless Connector                  | Yes                       |
| Wire Type                           | Stranded                  |
| <b>COMMUNICATIONS</b>               |                           |
| Network Speed                       | 10Gbps                    |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | RJ45 (MALE)               |
| Side B - Connector 1                | RJ45 (MALE)               |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Certifications                      | RoHS Compliant            |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>