

## SFP+ 10Gbase-CU Passive Twinax Copper Cable, SFP-H10GB-CU1-5M Compatible, Black, 5 ft. (1.52 m)

MODEL NUMBER: N280-005-BK



### Features

- 1.5 m. (5 ft.) 30Awg SFP+ High Speed Passive Copper 10Gbps Cable
- Fully compliant to MSA SFF-8431 specification
- Equivalent to Cisco SFP-H10GB-CU1-5M (See the Support tab on this web page for additional cross references)
- Use in 10Gbps Ethernet and Fibre Channel applications
- 100ohm Twinaxial cable, Diecast metal shells, pull-to-release latching
- Support for 1x, 2x, 4x and 8x Fiber Channel data rates
- Hot-Pluggable SFP 20PIN footprint
- Low power consumption

### Highlights

- 1.5 m. (5 ft.) 30AWG SFP+ High Speed Passive Copper 10Gbps Cable
- Fully compliant to MSA SFF-8431 specification
- Equivalent to Cisco SFP-H10GB-CU1-5M
- Low Cost alternative to Fiber Optic

### System Requirements

Tripp Lite SFP+ Direct Attach Cable ( DAC ) Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:

QLOGIC \* EMULEX \* JUNIPER \* ARISTA \* IBM \* DELL \* EXTREME EMC \* BROADCOM \* FINISAR \* VOLTAIRE \* CISCO

### CONFIRMED EQUIPMENT LIST (

\*ensure the latest firmware and software is installed )

CISCO NEXUS \*

CISCO CATALYST \*

CISCO CATALYST 3750x

CISCO CATALYST 2960

CISCO CATALYST 3500

CISCO CATALYST 3550

CISCO NEXUS 5010

ARISTA 70505-64

QUANTA T3048

EXTREME X250E

JUNIPER EX3200

NOT COMPATIBLE TO 3RD

PARTY CABLES: HP and

BROCADE

### Package Includes

- 1.5 m. (5 ft.) 30Awg SFP+ High Speed Passive Copper 10Gbps

Cable

## Specifications

OVERVIEW	
UPC Code	037332178138
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	4.2mm
Wire Gauge (AWG)	30
Cable Length (ft.)	5
Cable Length (m)	1.52
Cable Length (in.)	60
Cable Length (cm)	152.4
Minimum Bend Radius	23mm
Shipping Dimensions (hwd / in.)	12.00 x 10.50 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 26.67 x 1.27
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Operating Humidity Range	5% to 85% RH
Storage Humidity Range	5% to 85% RH
COMMUNICATIONS	
Network Compatibility	10 Gbps
IEEE Standards Supported	802.3BA
CONNECTIONS	
Side A - Connector 1	SFP+ (MALE)

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Side B - Connector 1	SFP+ (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.