

## QSFP+ to QSFP+ 40Gb Passive DAC Copper Infiniband Cable, 0.5M (20-in.)

MODEL NUMBER: N282-20N-BK



### Features

- 0.5M (20-in.) QSFP+ to QSFP+ 40Gb Passive DAC Copper Infiniband cable
- Meets or Exceeds strict 40-Gigabit Ethernet 40GBase-CR4 standards
- SDR, DDR, and QDR Compatible
- QSFP+ to QSFP+ 30AWG SFF-8436 compliant cable and connector
- Up to 10.3125 Gbps transfer rate per channel ( 40Gb aggregate )
- Multi-platform support for 40Gb, SAS, Fibre Channel, and SONET
- Zinc die-cast QSFP+ connectors with "Pull-to-Release" latching
- Fully compliant to latest QSFP+ MSA ( Multi Source Agreement )
- Lower port cost and reduced power budget vs Fiber Optics
- RoHS, SFF-8436, and IEEE 802.3ba Compliant
- BER better than 10<sup>12</sup>

## Specifications

OVERVIEW	
UPC Code	037332186096
Technology	SFP+/QSPP+/QSFP28
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	6.5mm

### Highlights

- 40Gbps QSFP+ to QSFP+ 0.5M (20-in.) patch cable
- Meets or Exceeds 40-Gigabit Ethernet 40GBASE-CR4 standards
- Fully compliant to the latest QSFP+ MSA (Multi Source Agreement)
- SDR, DDR, and QDR Compatible

### System Requirements

- Networking Switch or other hardware with open QSFP+ Port(s)

### Package Includes

- 0.5M (20-in.) QSFP+ to QSFP+ High Speed Passive Copper 40GB Cable



Cable Jacket Material	PVC
Wire Gauge (AWG)	30
Cable Length (ft.)	1.7
Cable Length (m)	0.51
Cable Length (in.)	20
Cable Length (cm)	50.80
Minimum Bend Radius	38mm
Shipping Dimensions (hwd / cm)	30.48 x 26.67 x 1.27
Shipping Dimensions (hwd / in.)	12.00 x 10.50 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.23
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0 to +70
Storage Temperature Range	-20 to +85
Operating Humidity Range	5% to 85% RH
Storage Humidity Range	5% to 85% RH
<b>COMMUNICATIONS</b>	
Network Speed	40 Gbps
IEEE Standards Supported	802.3BA
<b>CONNECTIONS</b>	
Side A - Connector 1	QSFP+ (MALE)
Side B - Connector 1	QSFP+ (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	MSA SFF-8436 and RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>