

# Cisco-Compatible GLC-LH-SMD SFP Transceiver - 10/100/1000Base-LX/LH, DDM, Singlemode LC, 1310 nm, 10 km

MODEL NUMBER: N286-01GLCLHSMD



Links a singlemode Gigabit Ethernet network cable to a Cisco router, server or switch's SFP port.

## Features

**SFP Transceiver Designed for Connection to Your Cisco Network Switch or Server** This SFP transceiver allows you to connect an 9/125 singlemode fiber optic cable to a 10/100/1000 Mbps network router, server or switch. It transmits data up to 10 kilometers (6.2 miles) and supports bi-directional Gigabit Ethernet communication up to 1.25 Gbps. The metal housing protects against electromagnetic interference (EMI) and excessive power dissipation.

**Functionally Equivalent to Cisco GLC-LH-SMD Transceiver Module** The MSA-compliant N286-01GLCLHSMD functions just like the equivalent Cisco GLC-LH-SMD transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the GLC-LH-SMD.

**Hot-Swappable for Installation Without Network Interruption** This input/output device is fully hot-swappable, so you can install it without a potentially costly 10/100/1000 Mbps network shutdown or device reboot. Just plug the SFP end of the transceiver into your Cisco network device. The other end has an LC duplex connector to link with singlemode fiber optic cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

**Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring** DDM support lets you keep track of various operating statuses in real time, including transceiver temperature, input and output power, and supply voltage.

## Specifications

OVERVIEW	
UPC Code	037332249289
Brand Compatibility	Cisco
CONNECTIONS	

## Highlights

- SFP transceiver module 100% compatible with Cisco's equivalent module
- Provides 1 Gbps throughput up to 10 km (6.2 mi.) via singlemode fiber cabling
- LC duplex female connector supports 1000Base-LX/LH signal at 1310 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

## Applications

- Install an additional LC duplex port on a Cisco router, server or switch for the purpose of connecting a singlemode Gigabit Ethernet network cable

## System Requirements

- Cisco or other compatible network router, server or switch

## Package Includes

- N286-01GLCLHSMD Cisco-Compatible GLC-LH-SMD SFP Transceiver
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	SFP (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	0.330 x 2.180 x 0.530
Unit Weight (lbs.)	0.064
Unit Weight (kg)	0.03
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
Operating Temperature	32 to 158 F (0 to 70 C)
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit)
Wavelength	1310nm
Transmission Distance	10 km
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	1 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Optical Port	LC
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.