

# Juniper-Compatible JNP-QSFP-100G-SR4 QSFP28 Transceiver - 100GBase-SR4, MTP/MPO MMF, 100 Gbps, 850 nm, 100 m (328 ft.)

MODEL NUMBER: N286-100G-SR4SJ



Connects a multimode Gigabit Ethernet fiber optic network cable to a Juniper switch or server's QSFP28 port.

## Features

### QSFP28 Transceiver for Connecting to Your Juniper Network Switch or Server

This QSFP28 transceiver allows you to connect a multimode fiber optic cable to a 100 Gbps network router, server or switch. It transmits data up to 100 meters (328 feet) using an 850 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

### Functionally Equivalent to Juniper JNP-QSFP-100G-SR4 Transceiver Module

The MSA-compliant N286-100G-SR4SJ functions just like the equivalent Juniper JNP-QSFP-100G-SR4 transceiver module and is manufactured to meet or exceed Juniper specifications. You can use this transceiver with any compatible Juniper router, server or switch and receive the same performance as the JNP-QSFP-100G-SR4.

### Hot-Swappable for Installation Without Network Interruption

This input/output device is fully hot-swappable, so you can install it without a potentially costly 100 Gbps network shutdown or device reboot. Just plug the QSFP28 end of the transceiver into your Juniper network device. The other end has an MTP/MPO connector to link with multimode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

### Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring

DDM support lets you keep track of operating information in real time, such as transceiver temperature, input and output power and supply voltage.

## Highlights

- QSFP28 transceiver module 100% compatible with Juniper's JNP-QSFP-100G-SR4
- Provides 100 Gbps throughput up to 100 m via multimode fiber cabling
- 12-strand MTP/MPO connector supports 100GBase-SR4 signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

## Package Includes

N286-100G-SR4SJ QSFP28 Transceiver

## Specifications

OVERVIEW	
UPC Code	037332284105
Brand Compatibility	Juniper



Powering Business Worldwide

TRIPP LITE  
SERIES

Technology	Fiber; Multimode
Optical Mode	OM4
Mode Type	Multimode
<b>CONNECTIONS</b>	
Side A - Connector 1	QSFP28 (MALE)
Side B - Connector 1	12-STRAND MTP/MPO (MALE)
Connector Material	Zinc Alloy
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	0.70 x 3.10 x 5.70
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.700 x 3.100 x 5.700
Unit Weight (lbs.)	0.1102
Unit Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 185°F (-10° to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Maximum Data Rate	100 Gbps
Network Compatibility	100 Gbps
Wavelength	840nm; 850nm; 860nm
Transmission Distance	100 m
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	100 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Driver Required	No
Optical Port	MPO/MTP
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	EN 55032; IEC/EN 63000
Product Compliance	RoHS; CE (Europe); FCC Part 15 Class B (USA); UKCA
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.