

Cisco-Compatible SFP-10G-LR-S SFP+ Transceiver - 10GBase-LR, DDM, Singlemode LC, 1310 nm, 10 km (6.1 mi.)

MODEL NUMBER: N286-10G-LR-S



Links a singlemode Gigabit Ethernet network cable to a Cisco router, server or switch's SFP port.

Features

SFP+ Transceiver Designed for Connection to Your Cisco Network Switch or Server This SFP+ transceiver allows you to connect an 9/125 singlemode fiber optic cable to a 10 Gbps network router, server or switch. It transmits data up to 10 kilometers (721 feet) and supports bi-directional Gigabit Ethernet communication up to 11.1 Gbps. The metal housing protects against electromagnetic interference (EMI) and excessive power dissipation.

Functionally Equivalent to Cisco SFP-10G-LR-S Transceiver Module The MSA-compliant N286-10G-LR-S functions just like the equivalent Cisco SFP-10G-LR-S transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the SFP-10G-LR-S.

Hot-Swappable for Installation Without Network Interruption This input/output device is fully hot-swappable, so you can install it without a potentially costly 10 Gbps network shutdown or device reboot. Just plug the SFP+ end of the transceiver into your Cisco network device. The other end has an LC duplex connector to link with singlemode fiber optic cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring DDM support lets you keep track of various operating statuses in real time, including transceiver temperature, input and output power, and supply voltage.

S-Class Transceiver Highly Recommended for Enterprise Network This S-Class fiber transceiver module is ideal for enterprise network runs of shorter distances than other standard modules. The S-Class N286-10G-LR-S supports only Ethernet protocol and operates only within commercial temperature ranges (0 to 70°C).

Specifications

Highlights

- SFP+ transceiver module 100% compatible with Cisco's equivalent module
- Provides 10 Gbps throughput up to 10 km (6.1 mi.) via singlemode fiber cabling
- LC duplex female connector supports 10GBase-LR signal at 1310 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

Applications

- Install an additional LC duplex port on a Cisco router, server or switch for the purpose of connecting a singlemode Gigabit Ethernet network cable

System Requirements

- Cisco or other compatible network router, server or switch

Package Includes

- N286-10G-LR-S Cisco-Compatible SFP-10G-LR-S SFP+ Transceiver
- Quick Start Guide



OVERVIEW	
UPC Code	037332249241
Brand Compatibility	Cisco
PHYSICAL	
Unit Dimensions (hwd / in.)	0.49 x 2.3 x 0.55
Unit Weight (lbs.)	0.064
Unit Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 °F (0 to 70 °C)
Storage Temperature Range	-40 to 185°F (-40 to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
Operating Temperature	32 to 158 °F (0 to 70 °C)
COMMUNICATIONS	
Network Compatibility	10 Gbps
Wavelength	1310nm
Transmission Distance	10 km
CONNECTIONS	
Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
FEATURES & SPECIFICATIONS	
Data Transfer Rate	10 Gbps
Optical Port	LC
Multi-Source Agreement (MSA) Compliant	Yes
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>